

Product datasheet

Specifications



Motor circuit protector, PowerPacT H, unit mount, 30A, 3 pole, 25kA, 600 VAC, 80% rated

HJL36030M71

Discontinued on: 9 Feb 2023

Discontinued

Main

Range	PowerPact
Product Name	PowerPact H
Product Or Component Type	Motor Circuit Protector
Device Application	Distribution

Complementary

[In] Rated Current	30 A
Number Of Poles	3P
Protected Poles Description	3t
Control Type	Toggle
Breaking Capacity Code	J
Breaking Capacity	100 kA at 240 V AC 50/60 Hz conforming to UL 489 65 kA at 480 V AC 50/60 Hz conforming to UL 489 25 kA at 600 V AC 50/60 Hz conforming to UL 489 20 kA at 250 V DC conforming to UL 489
[Ue] Rated Operational Voltage	690 V AC 50/60 Hz conforming to IEC 60947-3
Network Frequency	50/60 Hz
[Ics] Rated Service Breaking Capacity	65 kA at 220/240 V AC 50/60 Hz conforming to IEC 60947-2 35 kA at 380/440/415 V AC 50/60 Hz conforming to IEC 60947-2 18 kA at 500/525 V AC 50/60 Hz conforming to IEC 60947-2 20 kA at 250 V DC conforming to IEC 60947-2 20 kA at 500 V DC conforming to IEC 60947-2
[Uimp] Rated Impulse Withstand Voltage	8 kV conforming to IEC 60947-2
Trip Unit Technology	Thermal-magnetic
[Ith] Conventional Free Air Thermal Current	1.5...25 A
Magnetic Tripping Current	9...325 A
Continuous Current Rating	80 %
[Ui] Rated Insulation Voltage	750 V conforming to IEC 60947-2
Suitability For Isolation	Yes conforming to IEC 60947-2
Utilisation Category	Category A
Awg Gauge	AWG 14...AWG 3/0 aluminium/copper terminal
Mounting Mode	Unit mount (lug)
Mounting Support	Lug

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Electrical Connection	Lugs, line Lugs, load
Terminal Identifier	AL150HD
Tightening Torque	5 N.m for 2.5...6 mm² (AWG 14...AWG 10) 14 N.m for 10...95 mm² (AWG 8...AWG 3/0)
Number Of Slots	2 slot(s) for auxiliary switch OF (plug-in) 1 slot(s) for alarm switch SD (plug-in) 1 slot(s) for overcurrent trip switch SDE (plug-in) 1 slot(s) for voltage release MN or MX (plug-in)
Power Wire Stripping Length	16 mm
Color	Black
Height	163 mm
Width	104 mm
Depth	86 mm
Net Weight	2.2 kg
Quantity Per Set	1
Communication Interface	Modbus Ethernet

Environment

Quality Labels	CE
Standards	UL CSA NEMA NOM-003-SCFI-2000 IEC 60947-2
Product Certifications	UL CSA NOM
Ip Degree Of Protection	Front cover: IP40 conforming to IEC 60529
Pollution Degree	3 conforming to IEC 60947-1
Ambient Air Temperature For Operation	-25...70 °C
Ambient Air Temperature For Storage	-50...85 °C
Operating Altitude	< 2000 m without derating 5000 m with derating

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	14.478 cm
Package 1 Width	18.796 cm
Package 1 Length	22.098 cm
Package 1 Weight	1.985 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.




[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

 Mercury Free	
 Rohs Exemption Information	Yes
 Pvc Free	

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information