Product datasheet

Specification





Circuit breaker, PowerPacT H, thermal magnetic, unit mount, 150A, 3 pole, 25 kA, 600 VAC, 80% rated

HJL36150



! Discontinued on: 9 Feb 2023

Main

Range	PowerPact
Product Name	PowerPact H
Product Or Component Type	Circuit breaker
Device Application	Distribution

Complementary

Complementary	
[In] Rated Current	150 A
Number Of Poles	3P
Protected Poles Description	3t
Control Type	Toggle
Breaking Capacity Code	J
Breaking Capacity	100 kA at 240 V AC 50/60 Hz conforming to UL 489 65 kA at 480 V AC 50/60 Hz conforming to UL 489 25 kA at 600 V AC 50/60 Hz conforming to UL 489 20 kA at 250 V DC conforming to UL 489
[Ue] Rated Operational Voltage	690 V AC 50/60 Hz conforming to IEC 60947-3
Network Frequency	50/60 Hz
[Ics] Rated Service Breaking Capacity	65 kA at 220/240 V AC 50/60 Hz conforming to IEC 60947-2 35 kA at 380/440/415 V AC 50/60 Hz conforming to IEC 60947-2 18 kA at 500/525 V AC 50/60 Hz conforming to IEC 60947-2 20 kA at 250 V DC conforming to IEC 60947-2 20 kA at 500 V DC conforming to IEC 60947-2
[Uimp] Rated Impulse Withstand Voltage	8 kV conforming to IEC 60947-2
Trip Unit Technology	Thermal-magnetic
Magnetic Tripping Current	1700 A
Magnetic Hold Current	900 A
Continuous Current Rating	80 %
[Ui] Rated Insulation Voltage	750 V conforming to IEC 60947-2
Suitability For Isolation	Yes conforming to IEC 60947-2
Utilisation Category	Category A
Awg Gauge	AWG 14AWG 3/0 aluminium/copper terminal
Local Signalling	Switched off (OFF): 1 trip indicator (green)
Mounting Mode	Unit mount (lug)

Mounting Support	Lug	
Electrical Connection	Lugs, line Lugs, load	
Terminal Identifier	AL150HD	
Tightening Torque	5 N.m for 2.56 mm² (AWG 14AWG 10) 14 N.m for 1095 mm² (AWG 8AWG 3/0)	
Number Of Slots	2 slot(s) for auxiliary switch OF (plug-in) 1 slot(s) for alarm switch SD (plug-in) 1 slot(s) for overcurrent trip switch SDE (plug-in) 1 slot(s) for voltage release MN or MX (plug-in)	
Power Wire Stripping Length	16 mm	
Color	Black	
Height	163 mm	
Width	104 mm	
Depth	86 mm	
Net Weight	2.2 kg	
Quantity Per Set	1	
Communication Interface	Modbus Ethernet	
Circuit Breaker Application	HACR rated	

Environment

Quality Labels	CE
Standards	UL CSA NEMA NOM-003-SCFI-2000 IEC 60947-2
Product Certifications	UL CSA NOM
Ip Degree Of Protection	Front cover: IP40 conforming to IEC 60529
Pollution Degree	3 conforming to IEC 60947-1
Ambient Air Temperature For Operation	-2570 °C
Ambient Air Temperature For Storage	-5085 °C
Operating Altitude	< 2000 m without derating 5000 m with derating

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	19.304 cm
Package 1 Width	14.478 cm
Package 1 Length	22.352 cm
Package 1 Weight	1.882 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

	Mercury Free	
⊘	Rohs Exemption Information	Yes
⊘	Pvc Free	

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information