Product datasheet

Specifications





Control Relay with 24VDC Coil with 4 NO Contacts

8501XDO40V53

(!) Discontinued

Main

Range	8501X	
Relay Type	Control	
Product	Relay	
Current Rating	10 A AC 5 A DC	

Complementary

Coil Voltage	24 V DC
Control Circuit Voltage Limits	Operational: 0.81.1 Uc DC
Rated Breaking Capacity	6 A at 120 V AC for inductive control circuit conforming to UL 508 3 A at 240 V AC for inductive control circuit conforming to UL 508 1.5 A at 480 V AC for inductive control circuit conforming to UL 508 1.2 A at 600 V AC for inductive control circuit conforming to UL 508 10 A at <= 600 V AC for resistive control circuit conforming to UL 508 1.1 A at 125 V DC for inductive control circuit conforming to UL 508 0.55 A at 250 V DC for inductive control circuit conforming to UL 508 0.2 A at 301600 V DC for inductive control circuit conforming to UL 508 4 A at 125 V DC for resistive control circuit conforming to UL 508 0.8 A at 250 V DC for resistive control circuit conforming to UL 508
[Icm] Rated Short-Circuit Making Capacity	60 A at: 120 V AC for inductive load control circuit conforming to UL 508 30 A at: 240 V AC for inductive load control circuit conforming to UL 508 15 A at: 480 V AC for inductive load control circuit conforming to UL 508 12 A at: 600 V AC for inductive load control circuit conforming to UL 508 10 A at: <= 600 V AC for resistive load control circuit conforming to UL 508 1.1 A at: 125 V DC for inductive load control circuit conforming to UL 508 0.55 A at: 250 V DC for inductive load control circuit conforming to UL 508 0.2 A at: 301600 V DC for inductive load control circuit conforming to UL 508 4 A at: 125 V DC for inductive load control circuit conforming to UL 508 0.8 A at: 250 V DC for resistive load control circuit conforming to UL 508
Inrush Power In W	18 W
Hold-In Power Consumption In W	18 W
Operating Time	37 ms - pick-up 21 ms - drop-out
Contact Configuration	4 NO 4 standard contact cartridges
Electrical Connection	Screw clamp terminals
Awg Gauge	AWG 18AWG 12 copper
Tightening Torque	Control circuit: 1.021.36 N.m - on screw terminals
Mounting Type	Panel
Height	90.42 mm
Width	56.64 mm

Life Is On Schneider

Depth 131.32 mm

Environment

Operating Temperature	-4071 °C
Certifications	UL listed file E78403 CCN NKCR CSA LR60905 class 3211 03

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.1 cm
Package 1 Width	11.9 cm
Package 1 Length	23.4 cm
Package 1 Weight	1.49 kg
Unit Type Of Package 2	PAL
Number Of Units In Package 2	252
Package 2 Height	101.6 cm
Package 2 Width	101.6 cm
Package 2 Length	121.92 cm
Package 2 Weight	386.46 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile