Product datasheet





integrated servo motor- 1.7 Nm-6000 rpm- keyed shaft- multiturnwith brake-IP65

ILM0702P32F0000

! Discontinued on: 9 Feb 2023

① Discontinued

EAN Code: 3606485293905

Main

Range Of Product	PacDrive 3
Product Or Component Type	Servo motor integrated drive
Device Short Name	ILM

Complementary

[Us] Rated Supply Voltage	250700 V	
Continuous Stall Current	2.5 A	
Continuous Stall Torque	1.7 N.m	
Peak Stall Torque	7.6 N.m	
Nominal Output Power	720 W	
Nominal Torque	1.15 N.m	
Nominal Speed	6000 rpm	
Maximum Current Irms	11.8 A	
[In] Rated Current	1.5 A	
Shaft End	Keyed	
Second Shaft	Without second shaft end	
Shaft Diameter	11 mm	
Shaft Length	23 mm	
Key Width	18 mm	
Feedback Type	Absolute multiturn SinCos Hiperface	
Speed Feedback Resolution	128 periods	
Holding Brake	With	
Holding Torque	3 N.m holding brake	
Mounting Support	upport International standard flange	
Motor Flange Size	70 mm	
Torque Constant	0.76 N.m/A at 120 °C	
Back Emf Constant	48 V/krpm at 20 °C	
Number Of Motor Poles	6	
Rotor Inertia	0.51 kg.cm²	
Stator Resistance	4.2 Ohm at 20 °C for Ph/Ph 2.92 Ohm at 120 °C for Ph/N	

Stator Inductance	19 mH at 20 °C for Ph/Ph
	9.5 mH at 120 °C for Ph/N
Maximum Radial Force Fr	710 N at 1000 rpm
	560 N at 2000 rpm
	490 N at 3000 rpm
	450 N at 4000 rpm
	410 N at 5000 rpm
	390 N at 6000 rpm
Maximum Axial Force Fa	0.2 x Fr
Type Of Cooling	Natural convection
Length	252 mm
Number Of Motor Stacks	2
Centring Collar Diameter	60 mm
Centring Collar Depth	2.5 mm
Number Of Mounting Holes	4
Mounting Holes Diameter	5.5 mm
Circle Diameter Of The Mounting Holes	82 mm
Net Weight	3.7 kg

Environment

Ip Degree Of Protection IP65

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	21.0 cm
Package 1 Width	18.0 cm
Package 1 Length	35.6 cm
Package 1 Weight	4.28 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
⊘	Mercury Free	
Ø	Rohs Exemption Information	Yes
⊘	Pvc Free	

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information