
# **Product datasheet**

Specifications





# CANALIS KR 4X0800AL LONG FEED UNIT EL1

KRA0800EL41

EAN Code: 3606480953934

#### Main

Range	Canalis	
Product Name	KR	
Product Or Component Type	Long feeder trunking	
Device Short Name	KRA	
Product Specific Application	Oil and gas Mining minerals and metals Water and waste water Real estate and office buildings Healthcare Enterprise data centres	
Device Application	Feeder length	
Supply	Oil-immersed transformer Switchboard	
Material	Aluminium	
[le] Rated Operational Current	800 A at 35 °C	
Busbar/Connection Pads Direction Type	Flat to perpendicular	
Earth Conductor	Standard earth	
Short-Circuit Level	Standard version	

### Complementary

Housing Material	Mineral epoxy resin
Contacts Material	Tinned aluminium
[Ue] Rated Operational Voltage	1000 V
Network Frequency	50/60 Hz
[Ui] Rated Insulation Voltage	1000 V
[Icw] Rated Short-Time Withstand Current	27 kA
[Ipk] Rated Peak Withstand Current	56 kA
Radiated Magnetic Field	8.79 mT
Thermal Stress Limit	729000 kA².s
Maximum Voltage Drop	<0.0166 V with power factor = 1 at 50 Hz with 1A for 100 m long <0.0169 V with power factor = 0.9 at 50 Hz with 1A for 100 m long <0.016 V with power factor = 0.8 at 50 Hz with 1A for 100 m long <0.0149 V with power factor = 0.7 at 50 Hz with 1A for 100 m long
Mounting Location	Indoor Outdoor
Busbar Incoming	Horizontal side

Polarity	3L + N or 3L + PE or 3L + PEN
Product Certifications	CE ATEX EAC
Standards	IEC 61439-6
Dimension Type	Fix
Connection Pitch	115 mm
Colour	Grey (RAL 7030)
Linear Load	22 kg/m

#### Environment

Ip Degree Of Protection	IP68 conforming to IEC 60529
Ik Degree Of Protection	IK10 conforming to IEC 62262
Pollution Degree	3
Fire Resistance	760 °C 180 min conforming to IEC 60331-1
Derating Factor	035 °C (100 % of In)
	3540 °C (96 % of In)
	40…45 °C (89 % of In)
	4550 °C (84 % of In)
	5055 °C (78 % of In)
Operating Altitude	1000 m 100 % of In (indoor)
	2000 m 99 % of In (indoor)
	3000 m 96 % of In (indoor)
	4000 m 90 % of In (indoor)
	1000 m 98 % of In (outdoor)
	2000 m 94 % of In (outdoor)
	3000 m 89 % of In (outdoor)
	4000 m 83 % of In (outdoor)
Environmental Characteristic	EMC directive conforming to IEC 61439-6

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	29.0 cm
Package 1 Width	9.0 cm
Package 1 Length	85.0 cm
Package 1 Weight	23.1 kg

## **Contractual warranty**

Warranty

18 months

### Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes
Halogen Free Product

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information