

# Product datasheet

Specifications



## Acti9 iC60H 4P 40A B Miniature Circuit breaker

Local distributor code: 396790804 A9F53440

### Main

Range	Acti 9
Product name	Disbo iC60
Product or component type	Miniature circuit-breaker
Device short name	IC60H
Poles description	4P
Number of protected poles	4
[In] rated current	40 A
Network type	AC
Trip unit technology	Thermal-magnetic
Curve code	B
Breaking capacity	10 kA Icu at 100...133 V DC conforming to EN/IEC 60947-2 10000 A Icn at 415 V AC 50/60 Hz conforming to EN/IEC 60898-1 42 kA Icu at 12...133 V AC 50/60 Hz conforming to EN/IEC 60947-2 30 kA Icu at 220...240 V AC 50/60 Hz conforming to EN/IEC 60947-2 15 kA Icu at 380...415 V AC 50/60 Hz conforming to EN/IEC 60947-2 10 kA Icu at 440 V AC 50/60 Hz conforming to EN/IEC 60947-2
Utilisation category	Category A conforming to EN/IEC 60947-2

### Complementary

Network frequency	50/60 Hz
[Ue] rated operational voltage	440 V AC 50/60 Hz
Magnetic tripping limit	4 x In +/- 20 %
[Ics] rated service breaking capacity	21 kA 50 % conforming to EN/IEC 60947-2 - 12...133 V AC 50/60 Hz 15 kA 50 % conforming to EN/IEC 60947-2 - 220...240 V AC 50/60 Hz 7.5 kA 50 % conforming to EN/IEC 60947-2 - 380...415 V AC 50/60 Hz 5 kA 50 % conforming to EN/IEC 60947-2 - 440 V AC 50/60 Hz 7500 A 75 % conforming to EN/IEC 60898-1 - 415 V AC 50/60 Hz 10 kA 100 % conforming to EN/IEC 60947-2 - 100...133 V DC
Limitation class	3 conforming to EN/IEC 60947-2
[Ui] rated insulation voltage	500 V AC 50/60 Hz conforming to EN/IEC 60947-2
[Uimp] rated impulse withstand voltage	6 kV conforming to EN/IEC 60947-2
Contact position indicator	Yes
Control type	Toggle
Local signalling	Trip indicator

<b>Mounting mode</b>	Clip-on
<b>Mounting support</b>	Rail
<b>9 mm pitches</b>	8
<b>Height</b>	85 mm
<b>Width</b>	72 mm
<b>Depth</b>	78.5 mm
<b>Net weight</b>	0.5 kg
<b>Colour</b>	White
<b>Mechanical durability</b>	20000 cycles
<b>Electrical durability</b>	10000 cycles
<b>Provision for padlocking</b>	Padlockable
<b>Connections - terminals</b>	Single terminal (top or bottom) 1...35 mm <sup>2</sup> rigid Single terminal (top or bottom) 1...25 mm <sup>2</sup> flexible
<b>Wire stripping length</b>	14 mm for top or bottom connection
<b>Tightening torque</b>	3.5 N.m top or bottom
<b>Earth-leakage protection</b>	Separate block

## Environment

<b>Standards</b>	EN/IEC 60947-2 EN/IEC 60898-1
<b>IP degree of protection</b>	IP20 conforming to IEC 60529
<b>Pollution degree</b>	3 conforming to EN/IEC 60947-2
<b>Tropicalisation</b>	2 conforming to IEC 60068-1
<b>Relative humidity</b>	95 % at 55 °C
<b>Ambient air temperature for operation</b>	-35...70 °C
<b>Ambient air temperature for storage</b>	-40...85 °C

## Packing Units

<b>Unit Type of Package 1</b>	PCE
<b>Number of Units in Package 1</b>	1
<b>Package 1 Weight</b>	492 g
<b>Package 1 Height</b>	7.2 cm
<b>Package 1 width</b>	7.5 cm
<b>Package 1 Length</b>	9 cm
<b>Unit Type of Package 2</b>	BB1
<b>Number of Units in Package 2</b>	3
<b>Package 2 Weight</b>	1.539 kg
<b>Package 2 Height</b>	8.5 cm
<b>Package 2 width</b>	9.8 cm
<b>Package 2 Length</b>	22 cm
<b>Unit Type of Package 3</b>	S03
<b>Number of Units in Package 3</b>	33
<b>Package 3 Weight</b>	17.416 kg

Package 3 Height	30 cm
Package 3 width	30 cm
Package 3 Length	40 cm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Halogen content performance	Halogen free product

## Contractual warranty

Warranty	18 months
----------	-----------