Product datasheet

Specifications





TeSys D contactor - 3P(3 NO) -AC-3 - <= 440 V 95 A - 24 V AC 50/60 Hz coil

Local distributor code: 381821681

LC1D95B7

EAN Code: 3389110450651

Main

Range	TeSys
Range Of Product	TeSys Deca
Product Or Component Type	Contactor
Device Short Name	LC1D
Contactor Application	Motor control Resistive load
Utilisation Category	AC-3 AC-3e AC-4 AC-1
Poles Description	ЗР
[Ue] Rated Operational Voltage	Power circuit: <= 690 V AC 25400 Hz
[le] Rated Operational Current	95 A (at <60 °C) at <= 440 V AC-3 for power circuit 125 A (at <60 °C) at <= 690 V AC-1 for power circuit 95 A (at <60 °C) at <= 440 V AC-3e for power circuit
[Uc] Control Circuit Voltage	24 V AC 50/60 Hz

Complementary

Motor Power Kw	25 kW at 220230 V AC 50 Hz (AC-3)	
	45 kW at 380400 V AC 50 Hz (AC-3)	
	45 kW at 415440 V AC 50 Hz (AC-3)	
	55 kW at 500 V AC 50 Hz (AC-3)	
	45 kW at 660690 V AC 50 Hz (AC-3)	
	15 kW at 400 V AC 50 Hz (AC-4)	
	25 kW at 220230 V AC 50 Hz (AC-3e)	
	45 kW at 380400 V AC 50 Hz (AC-3e)	
	45 kW at 415440 V AC 50 Hz (AC-3e)	
	55 kW at 500 V AC 50 Hz (AC-3e)	
	45 kW at 660690 V AC 50 Hz (AC-3e)	
Motor Power Hp	7.5 hp at 120 V AC 60 Hz for 1 phase motors	
	15 hp at 230/240 V AC 60 Hz for 1 phase motors	
	30 hp at 200/208 V AC 60 Hz for 3 phases motors	
	30 hp at 230/240 V AC 60 Hz for 3 phases motors	
	60 hp at 460/480 V AC 60 Hz for 3 phases motors	
	60 hp at 575/600 V AC 60 Hz for 3 phases motors	
Compatibility Code	LC1D	
Pole Contact Composition	3 NO	
Protective Cover	With	
[Ith] Conventional Free Air	10 A (at 60 °C) for signalling circuit	
Thermal Current	125 A (at 60 °C) for power circuit	
Irms Rated Making Capacity	1100 A at 440 V AC for power circuit conforming to IEC 60947	
	140 A AC for signalling circuit conforming to IEC 60947-5-1	
	250 A DC for signalling circuit conforming to IEC 60947-5-1	

Rated Breaking Capacity	1100 A at 440 V for power circuit conforming to IEC 60947	
[Icw] Rated Short-Time Withstand Current	1100 A 40 °C - 1 s for power circuit 800 A 40 °C - 10 s for power circuit 400 A 40 °C - 1 min for power circuit 135 A 40 °C - 10 min for power circuit 140 A - 100 ms for signalling circuit 120 A - 500 ms for signalling circuit 100 A - 1 s for signalling circuit	
Associated Fuse Rating	10 A gG for signalling circuit conforming to IEC 60947-5-1 200 A gG at <= 690 V coordination type 1 for power circuit 160 A gG at <= 690 V coordination type 2 for power circuit	
Average Impedance	0.8 mOhm - Ith 125 A 50 Hz for power circuit	
Power Dissipation Per Pole	12.5 W AC-1 7.2 W AC-3 7.2 W AC-3e	
[Ui] Rated Insulation Voltage	Power circuit: 1000 V conforming to IEC 60947-4-1 Power circuit: 600 V CSA certified Power circuit: 600 V UL certified Signalling circuit: 690 V conforming to IEC 60947-1 Signalling circuit: 600 V CSA certified Signalling circuit: 600 V UL certified	
Overvoltage Category	III	
Pollution Degree	3	
[Uimp] Rated Impulse Withstand Voltage	8 kV conforming to IEC 60947	
Safety Reliability Level	B10d = 1.3 Mcycles contactor with nominal load conforming to EN/ISO 13849-1 B10d = 20 Mcycles contactor with mechanical load conforming to EN/ISO 13849-1	
Mechanical Durability	4 Mcycles	
Electrical Durability	1.2 Mcycles 95 A AC-3 1.3 Mcycles 125 A AC-1 1.2 Mcycles 95 A AC-3e	
Control Circuit Type	AC at 50/60 Hz standard	
Coil Technology	Without built-in suppressor module	
Control Circuit Voltage Limits	0.81.1 Uc (-4055 °C):operational AC 50 Hz 0.851.1 Uc (-4055 °C):operational AC 60 Hz 0.30.6 Uc (-4070 °C):drop-out AC 50/60 Hz 11.1 Uc (5570 °C):operational AC 50/60 Hz	
Inrush Power In Va	245 VA 60 Hz cos phi 0.75 (at 20 °C) 245 VA 50 Hz cos phi 0.75 (at 20 °C)	
Hold-In Power Consumption In Va	26 VA 60 Hz cos phi 0.3 (at 20 °C) 26 VA 50 Hz cos phi 0.3 (at 20 °C)	
Heat Dissipation	610 W at 50/60 Hz	
Operating Time	2035 ms closing 620 ms opening	
Maximum Operating Rate	3600 cyc/h 60 °C	

Connections - Terminals	Control circuit: screw clamp terminals 2 12.5 mm ² - cable stiffness: flexible with cable end
	Control circuit: screw clamp terminals 1 12.5 mm ² - cable stiffness: flexible with cable end
	Control circuit: screw clamp terminals 1 14 mm ² - cable stiffness: flexible without cable end
	Control circuit: screw clamp terminals 2 14 mm ² - cable stiffness: flexible without cable end
	Control circuit: screw clamp terminals 1 14 mm ² - cable stiffness: solid without cable end
	Control circuit: screw clamp terminals 2 14 mm ² - cable stiffness: solid without cable end
	Power circuit: connector 1 450 mm ² - cable stiffness: flexible without cable end Power circuit: connector 2 425 mm ² - cable stiffness: flexible without cable end Power circuit: connector 1 450 mm ² - cable stiffness: flexible with cable end Power circuit: connector 2 416 mm ² - cable stiffness: flexible with cable end Power circuit: connector 1 450 mm ² - cable stiffness: solid without cable end Power circuit: connector 2 425 mm ² - cable stiffness: solid without cable end Power circuit: connector 2 425 mm ² - cable stiffness: solid without cable end Power circuit: connector 2 425 mm ² - cable stiffness: solid without cable end
Tightening Torque	Control circuit: 1.2 N.m - on screw clamp terminals - with screwdriver flat Ø 6 mm Control circuit: 1.2 N.m - on screw clamp terminals - with screwdriver Philips No 2 Power circuit: 12 N.m - on connector - with screwdriver flat Ø 6 to Ø 8 mm Power circuit: 12 N.m - on connector hexagonal screw head 4 mm Control circuit: 1.2 N.m - on screw clamp terminals - with screwdriver pozidriv No 2
Auxiliary Contact Composition	1 NO + 1 NC
Auxiliary Contacts Type	type mechanically linked 1 NO + 1 NC conforming to IEC 60947-5-1 type mirror contact 1 NC conforming to IEC 60947-4-1
Signalling Circuit Frequency	25400 Hz
Minimum Switching Voltage	17 V for signalling circuit
Minimum Switching Current	5 mA for signalling circuit
Insulation Resistance	> 10 MOhm for signalling circuit
Non-Overlap Time	1.5 ms on de-energisation between NC and NO contact 1.5 ms on energisation between NC and NO contact
Mounting Support	Plate Rail

Environment

Standards	EN/IEC 60947-1 EN/IEC 60947-4-1 EN/IEC 60947-5-1 UL 60947-4-1 UL 60947-5-1 CSA C22.2 No 60947-4-1 CSA C22.2 No 60947-5-1 GB/T 14048.4
Product Certifications	IECEE CB Scheme UL CSA CCC EAC LROS (Lloyds register of shipping) RINA BV DNV-GL
Ip Degree Of Protection	IP20 front face conforming to IEC 60529
Protective Treatment	TH conforming to IEC 60068-2-30
Climatic Withstand	conforming to IACS E10 exposure to damp heat
Permissible Ambient Air Temperature Around The Device	-4060 °C 6070 °C with derating
Operating Altitude	03000 m
Fire Resistance	850 °C conforming to IEC 60695-2-1
Flame Retardance	V1 conforming to UL 94

Mechanical Robustness	Vibrations contactor open (2 Gn, 5300 Hz) Shocks contactor open (8 Gn for 11 ms) Vibrations contactor closed (3 Gn, 5300 Hz) Shocks contactor closed (10 Gn for 11 ms)	
Height	127 mm	
Width	85 mm	
Depth	130 mm	
Net Weight	1.61 kg	

Packing Units

PCE
1
9.5 cm
13.5 cm
14 cm
1.564 kg
S02
5
15 cm
30 cm
40 cm
8.275 kg
P06
80
80 cm
80 cm
60 cm
140.9 kg

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes
Pvc Free


Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations

Product datasheet

Dimensions Drawings

Dimensions



(1) Minimum electrical clearance

	D80	D95
	85	85
with LA4 D●2	135	135
with LA4 DB3 or LAD 4BB3	135	-
with LA4 DF, DT	142	142
with LA4 DM, DW, DL	150	150
without cover or add-on blocks	125	125
with cover, without add-on blocks	130	130
with LAD N (1 contact)	150	150
with LAD N or C (2 or 4 contacts)	158	158
with LA6 DK10, LAD 6DK	170	170
with LAD T, R, S	178	178
with LAD T, R, S and sealing cover	182	182
	with LA4 DB3 or LAD 4BB3 with LA4 DF, DT with LA4 DM, DW, DL without cover or add-on blocks with cover, without add-on blocks with LAD N (1 contact) with LAD N or C (2 or 4 contacts) with LA6 DK10, LAD 6DK with LAD T, R, S	85with LA4 D•2135with LA4 DB3 or LAD 4BB3135with LA4 DB3 or LAD 4BB3142with LA4 DF, DT142with LA4 DM, DW, DL150with out cover or add-on blocks125with cover, without add-on blocks130with LAD N (1 contact)150with LAD N or C (2 or 4 contacts)158with LA6 DK10, LAD 6DK170with LAD T, R, S178

Product datasheet

Connections and Schema

Wiring

