# **Product datasheet**

Specification





# TeSys F contactor - 4P (4 NO) - AC-1 - <= 440 V 200 A - coil 125 V DC

LC1F1154GD

! Discontinued on: 11 Jan 2023

(!) Discontinued

EAN Code: 3389118093409

### Main

Range	TeSys
Range Of Product	TeSys F
Product Or Component Type	Contactor
Device Short Name	LC1F
Contactor Application	Resistive load
Utilisation Category	AC-1
Poles Description	4P
[Ue] Rated Operational Voltage	<= 690 V AC 50/60 Hz <= 460 V DC
[Uc] Control Circuit Voltage	125 V DC
[le] Rated Operational Current	200 A (at <40 °C) at <= 440 V AC-1

## Complementary

Complementary	
[Uimp] Rated Impulse Withstand Voltage	8 kV
[Ith] Conventional Free Air Thermal Current	200 A (at 40 °C)
Rated Breaking Capacity	920 A conforming to IEC 60947-4-1
[Icw] Rated Short-Time Withstand Current	1100 A 40 °C - 10 s
Current	640 A 40 °C - 30 s
	520 A 40 °C - 1 min
	400 A 40 °C - 3 min
	320 A 40 °C - 10 min
Associated Fuse Rating	125 A aM at <= 440 V
	200 A gG at <= 440 V
Average Impedance	0.37 mOhm - Ith 200 A 50 Hz
[Ui] Rated Insulation Voltage	1000 V conforming to IEC 60947-4-1
	1500 V conforming to VDE 0110 group C
Power Dissipation Per Pole	15 W AC-1
Overvoltage Category	III
Power Pole Contact Composition	4 NO
Control Circuit Voltage Limits	Operational: 0.851.1 Uc (at 55 °C)
	Drop-out: 0.150.2 Uc (at 55 °C)
Mechanical Durability	10 Mcycles
Inrush Power In W	560 W (at 20 °C)
Hold-In Power Consumption In W	4.5 W at 20 °C

19 Apr 2024 Life Is On Schneider



Maximum Operating Rate	2400 cyc/h 55 °C
Operating Time	3040 ms closing
	3050 ms opening
Connections - Terminals	Power circuit: bar 2 cable(s) - busbar cross section: 20 x 3 mm
	Power circuit: lugs-ring terminals 1 cable(s) 95 mm <sup>2</sup>
	Power circuit: connector 1 cable(s) 95 mm <sup>2</sup>
	Control circuit: screw clamp terminals 1 cable(s) 14 mm²flexible without cable end
	Control circuit: screw clamp terminals 2 cable(s) 14 mm²flexible without cable end
	Control circuit: screw clamp terminals 1 cable(s) 14 mm²flexible with cable end
	Control circuit: screw clamp terminals 2 cable(s) 12.5 mm²flexible with cable end
	Control circuit: screw clamp terminals 1 cable(s) 14 mm <sup>2</sup> solid without cable end
	Control circuit: screw clamp terminals 2 cable(s) 14 mm²solid without cable end
	Power circuit: bolted connection
Tightening Torque	Power circuit: 10 N.m
	Control circuit: 1.2 N.m
Mounting Support	Plate
Heat Dissipation	4.5 W
Standards	JIS C8201-4-1
	IEC 60947-1
	IEC 60947-4-1
	EN 60947-4-1
	EN 60947-1
Product Certifications	RINA
	BV
	UL
	ABS
	RMRoS
	СВ
	LROS (Lloyds register of shipping)
	DNV
	CCC
	UKCA
Compatibility Code	LC1F
Control Circuit Type	DC standard

## **Environment**

Ip Degree Of Protection	IP2X front face with shrouds conforming to IEC 60529 IP2X front face with shrouds conforming to VDE 0106	
Protective Treatment	тн	
Ambient Air Temperature For Operation	-4060 °C	
Ambient Air Temperature For Storage	-6080 °C	
Permissible Ambient Air Temperature Around The Device	6070 °C at Uc	
Height	162 mm	
Width	200.5 mm	
Depth	171 mm	
Operating Altitude	3000 m without derating	
Net Weight	3.83 kg	

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	22.0 cm
Package 1 Width	21.5 cm

Package 1 Length	26.5 cm
Package 1 Weight	4.85 kg

## **Contractual warranty**

Warranty 18 months

## Sustainability Screen Premium

**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance



Mercury Free



Rohs Exemption Information

Yes

### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information

19 Apr 2024