Product datasheet





TeSys D - star delta starter - 3 x 3P (3 NO) - 9 A - 24 V AC coil Local distributor code: 381824950 LC3D09AB7

EAN Code: 3389110545388

Main

Wall				
Range	TeSys TeSys Deca			
Product Name	TeSys Deca			
Product Or Component Type	Star delta starter			
Device Short Name	LC3D			
Contactor Application	Motor control			
Utilisation Category	AC-3			
Device Presentation	e Presentation Pre-wired			
Poles Description	3 x 3P			
Power Pole Contact Composition	3 x 3 NO			
[Ue] Rated Operational Voltage	Power circuit: <= 690 V AC 25400 Hz			
[le] Rated Operational Current	9 A (at <60 °C) at <= 440 V AC AC-3 for power circuit			
Motor Power Kw	4 kW at 220/230 V AC 50/60 Hz 7.5 kW at 380/400 V AC 50/60 Hz 7.5 kW at 415 V AC 50/60 Hz 7.5 kW at 440 V AC 50/60 Hz			
Control Circuit Type	AC at 50/60 Hz			
[Uc] Control Circuit Voltage 24 V AC 50/60 Hz				
Auxiliary Contact Composition 1 NC for KM1 star contactor				
[Uimp] Rated Impulse Withstand Voltage	6 kV conforming to IEC 60947			
Overvoltage Category	III			
[Ui] Rated Insulation Voltage	Power circuit: 690 V conforming to IEC 60947-4-1 Power circuit: 600 V CSA certified Power circuit: 600 V UL certified Signalling circuit: 600 V conforming to IEC 60947-1 Signalling circuit: 600 V CSA certified Signalling circuit: 600 V UL certified			
Electrical Durability	2 Mcycles 9 A AC-3 at Ue <= 440 V			
Safety Cover	Protective cover			
Interlocking Type	Mechanical			
Mounting Support	Plate			
Standards	EN 60947-5-1 UL 508 CSA C22.2 No 14 IEC 60947-5-1 IEC 60947-4-1 EN 60947-4-1 IEC 60335-1			

Product Certifications	CCC
	UL
	BV
	RINA
	GOST
	DNV
	GL
	CSA
	LROS (Lloyds register of shipping)

Complementary

Connections - Terminals	Power circuit: screw clamp terminals 1 14 mm ² - cable stiffness: flexible without
	cable end
	Power circuit: screw clamp terminals 2 14 mm ² - cable stiffness: flexible without cable end
	Power circuit: screw clamp terminals 1 14 mm² - cable stiffness: flexible with cable end
	Power circuit: screw clamp terminals 2 12.5 mm² - cable stiffness: flexible with cable end
	Power circuit: screw clamp terminals 1 14 mm² - cable stiffness: solid without cable end
	Power circuit: screw clamp terminals 2 14 mm² - cable stiffness: solid without cable end
	Control circuit: screw clamp terminals 1 14 mm² - cable stiffness: flexible without cable end
	Control circuit: screw clamp terminals 2 14 mm² - cable stiffness: flexible without cable end
	Control circuit: screw clamp terminals 1 14 mm² - cable stiffness: flexible with cable end
	Control circuit: screw clamp terminals 2 12.5 mm² - cable stiffness: flexible with cable end
	Control circuit: screw clamp terminals 1 14 mm² - cable stiffness: solid without cable end
	Control circuit: screw clamp terminals 2 14 mm² - cable stiffness: solid without cable end
Fightening Torque	Power circuit: 1.7 N.m - on screw clamp terminals - with screwdriver flat Ø 6 mm Power circuit: 1.7 N.m - on screw clamp terminals - with screwdriver Philips No 2
	Control circuit: 1.7 N.m - on screw clamp terminals - with screwdriver flat Ø 6 mm
	Control circuit: 1.7 N.m - on screw clamp terminals - with screwdriver Philips No 2
	Power circuit: 1.7 N.m - on screw clamp terminals - with screwdriver pozidriv No 2 Control circuit: 1.7 N.m - on screw clamp terminals - with screwdriver pozidriv No 2
Mechanical Durability	15 Mcycles
Maximum Operating Rate	30 cyc/h 60 °C
Starting Time	30 s
Coil Technology	Without built-in suppressor module
Control Circuit Voltage Limits	Drop-out: 0.30.6 Uc at 50/60 Hz (at <60 °C) Operational: 0.81.1 Uc at 50 Hz (at <60 °C) Operational: 0.851.1 Uc at 60 Hz (at <60 °C)
	Operational, 0.00 To Cat 00 TIZ (at 500 °C)
nrush Power In Va	70 VA 60 Hz cos phi 0.75 (at 20 °C) 70 VA 50 Hz cos phi 0.75 (at 20 °C)
Hold-In Power Consumption In Va	70 VA 50 Hz cos phi 0.75 (at 20 °C) 7.5 VA 60 Hz cos phi 0.3 (at 20 °C)
Hold-In Power Consumption In Va	70 VA 50 Hz cos phi 0.75 (at 20 °C) 7.5 VA 60 Hz cos phi 0.3 (at 20 °C) 7 VA 50 Hz cos phi 0.3 (at 20 °C)
Hold-In Power Consumption In Va	70 VA 50 Hz cos phi 0.75 (at 20 °C) 7.5 VA 60 Hz cos phi 0.3 (at 20 °C) 7 VA 50 Hz cos phi 0.3 (at 20 °C) 23 W at 50/60 Hz Mechanically linked conforming to IEC 60947-5-1 3 x 1 NO + 1 NC
Hold-In Power Consumption In Va Heat Dissipation Auxiliary Contacts Type Signalling Circuit Frequency	70 VA 50 Hz cos phi 0.75 (at 20 °C) 7.5 VA 60 Hz cos phi 0.3 (at 20 °C) 7 VA 50 Hz cos phi 0.3 (at 20 °C) 23 W at 50/60 Hz Mechanically linked conforming to IEC 60947-5-1 3 x 1 NO + 1 NC Mirror contact conforming to IEC 60947-4-1 3 x 1 NC
Hold-In Power Consumption In Va Heat Dissipation Auxiliary Contacts Type Signalling Circuit Frequency Minimum Switching Current Minimum Switching Voltage	70 VA 50 Hz cos phi 0.75 (at 20 °C) 7.5 VA 60 Hz cos phi 0.3 (at 20 °C) 7 VA 50 Hz cos phi 0.3 (at 20 °C) 23 W at 50/60 Hz Mechanically linked conforming to IEC 60947-5-1 3 x 1 NO + 1 NC Mirror contact conforming to IEC 60947-4-1 3 x 1 NC
Hold-In Power Consumption In Va Heat Dissipation Auxiliary Contacts Type Signalling Circuit Frequency Minimum Switching Current	70 VA 50 Hz cos phi 0.75 (at 20 °C) 7.5 VA 60 Hz cos phi 0.3 (at 20 °C) 7 VA 50 Hz cos phi 0.3 (at 20 °C) 23 W at 50/60 Hz Mechanically linked conforming to IEC 60947-5-1 3 x 1 NO + 1 NC Mirror contact conforming to IEC 60947-4-1 3 x 1 NC 25400 Hz 5 mA for signalling circuit

Height	124 mm
Depth	143 mm
Net Weight	1.53 kg

Environment

Insulation Resistance	> 10 MOhm for signalling circuit
Ip Degree Of Protection	IP20 front face conforming to IEC 60529
Climatic Withstand	conforming to IACS E10 conforming to IEC 60947-1 Annex Q category D
Protective Treatment	TH conforming to IEC 60068-2-30
Pollution Degree	3
Ambient Air Temperature For Storage	-6080 °C
Ambient Air Temperature For Operation	-4070 °C at Uc
Operating Altitude	3000 m without derating
Fire Resistance	850 °C conforming to IEC 60695-2-1
Flame Retardance	V1 conforming to UL 94
Mechanical Robustness	Vibrations contactor open: 2 Gn, 5300 Hz Vibrations contactor closed: 4 Gn, 5300 Hz Shocks contactor open: 10 Gn for 11 ms Shocks contactor closed: 15 Gn for 11 ms

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	16.0 cm
Package 1 Width	17.5 cm
Package 1 Length	23.5 cm
Package 1 Weight	1.58 kg

Contractual warranty

Warranty 18 months



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc
⊘	Toxic Heavy Metal Free
⊘	Mercury Free
⊘	Rohs Exemption Information Yes
⊘	Pvc Free


Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information

LC3D09AB7

Dimensions Drawings


Dimensions




LC:	3	D09A	D12A	D18A	D32A
а		143	143	144	165
b		26.5	26.5	26.5	32.5
С	with LAD S	139	139	139	145
	with LAD S and sealing cover	143	143	143	149

Connections and Schema

Wiring





- (1) Recommended cabling for reversal of motor rotation (standard motor, viewed from shaft end).
- (2) Remote control.

NOTE: LC3 D09A to D18A: Mechanical interlock between KM3 and KM1.

Product datasheet

LC3D09AB7