

Main

| | |
|---------------------------------------|---|
| Range of product | Modicon Optimized |
| Product or component type | Safety and isolation transformer |
| Rated power in VA | 400 VA |
| Input voltage | 230 V AC single phase, terminal(s): N-L1 400 V AC phase to phase, terminal(s): L1-L2 |
| Output voltage | 24 V AC |
| Secondary winding | Single |
| Protective cover | Without |
| Ambient air temperature for operation | -20...50 °C |

Complementary

| | |
|------------------------------------|---|
| Input voltage limits | 360...440 V 207...253 V |
| Network frequency limits | 47...63 Hz |
| Input voltage tolerance | +/- 15 V |
| Efficiency | 92 % |
| Power dissipation in W | 34.8 W |
| Output sustained overvoltage | 4 % (no load, hot state) |
| Maximum voltage drop at rated load | 0.7 % |
| No load losses | 12.4 W |
| Short-circuit voltage | 0,045 |
| Output protection type | Against overload, protection technology: external Against overvoltage, protection technology: external Against short-circuits, protection technology: external |
| Connections - terminals | For input connection: screw type terminals, connection capacity: 5 x 4 mm ² AWG 11 For input ground connection: screw type terminals, connection capacity: 1 x 4 mm ² AWG 11 For output connection: screw type terminals, connection capacity: 2 x 10 mm ² AWG 6 |
| Marking | CE |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|-----------------------------|--|
| Fixing mode | By 4 screws diameter: 5.8 mm on vertical panel, operating position: horizontal By 4 screws diameter: 5.8 mm on vertical panel, operating position: vertical By 4 screws diameter: 5.8 mm on horizontal panel with derating to 90 % |
| Operating altitude | 3000 m |
| Electrical insulation class | Class B |
| Width | 136 mm |
| Height | 140 mm |
| Depth | 120 mm |
| Net weight | 6.5 kg |

Environment

| | |
|-------------------------------------|--|
| Product certifications | EAC UR |
| Standards | UL 506 |
| IP degree of protection | IP20 |
| Environmental characteristic | EMC conforming to EN 62041 Safety conforming to EN 61558-1 Safety conforming to EN 61558-2-6 |
| Protective treatment | TC |
| Ambient air temperature for storage | -40...80 °C |
| Overvoltage category | Class I conforming to VDE 0106-1 |
| Dielectric strength | 2000 V between winding and ground 4000 V between primary and secondary |

Packing Units

| | |
|------------------------------|-----------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Weight | 6.834 kg |
| Package 1 Height | 19 cm |
| Package 1 width | 23 cm |
| Package 1 Length | 26.5 cm |
| Unit Type of Package 2 | P06 |
| Number of Units in Package 2 | 15 |
| Package 2 Weight | 115.51 kg |
| Package 2 Height | 80 cm |
| Package 2 width | 80 cm |
| Package 2 Length | 60 cm |


Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS declaration |
| Environmental Disclosure | Product Environmental Profile |
| PVC free | Yes |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Dimensions




Dimensions in mm

| a | b | c | G | J | Ø |
|-----|-----|-----|-----|----|-----|
| 135 | 136 | 120 | 104 | 87 | 5.8 |

Dimensions in in.

| a | b | c | G | J | Ø |
|------|------|------|------|------|------|
| 5.31 | 5.35 | 4.72 | 4.09 | 3.42 | 0.23 |

Internal Scheme



Primary Voltage Wiring



Secondary Voltage Wiring

