# **Product datasheet**

Specification





# regulated SMPS - 1 or 2-phase - 100..240 V AC - 5 V - 4 A

ABL8MEM05040

- ! Discontinued on: 11 Nov 2020
- ! End-of-service on: 25 Jan 2021

① Discontinued

EAN Code: 3389119405539

#### Main

Range Of Product	Modicon Power Supply	
Product Or Component Type	Power supply	
Power Supply Type	Regulated switch mode	
Nominal Input Voltage	100240 V AC phase to phase, terminal(s): L1-L2 100240 V AC single phase, terminal(s): N-L1 120250 V DC	
Rated Power In W	20 W	
Output Voltage	5 V DC	
Power Supply Output Current	4 A	

## Complementary

· · · · · · · · · · · · · · · · · ·			
Input Voltage Limits	85264 V AC		
Input Protection Type	Integrated fuse (not interchangeable)		
Inrush Current	20 A		
Power Factor	0.5 at 5 V DC		
Efficiency	75 %		
Output Voltage Adjustment	4.756.25 V adjustable		
Power Dissipation In W	6.7 W		
Current Consumption	0.35 A 240 V AC 0.55 A 100 V AC		
Residual Ripple	250 mV		
Output Protection Type	Against short-circuits		
Connections - Terminals  Screw type terminals: 2 x 0.142 x 2.5 mm², (AWG 26AWG 14) for connection  Screw type terminals: 4 x 0.144 x 2.5 mm², (AWG 26AWG 14) for connection			
Status Led	1 LED (green) output voltage		
Depth	59 mm		
	100 mm		
Width	54 mm		
Net Weight	0.195 kg		
Output Coupling	Parallel Series		

Marking	CE
Mounting Support	35 x 15 mm symmetrical DIN rail 35 x 7.5 mm symmetrical DIN rail panel 2 screws, diameter : 4 mm
Operating Position	Vertical
Supply	SELV conforming to EN/IEC 60950-1 SELV conforming to EN/IEC 60204-1 SELV conforming to IEC 60364-4-41
Dielectric Strength	3000 V with between input and output

## **Environment**

Standards	CSA C22.2 No 60950-1 UL 508 EN/IEC 62368-1			
Product Certifications	EAC TUV 60950-1 RCM KC CCSAus CSA 22-2 No 950 CULus 508			
Environmental Characteristic	EMC conforming to EN 55022 class B EMC conforming to EN 61000-6-3 EMC conforming to EN/IEC 61000-6-2 EMC conforming to EN/IEC 61204-3 Safety conforming to EN/IEC 60950-1			
Operating Altitude	erating Altitude 2000 m			
Ip Degree Of Protection	gree Of Protection IP20 conforming to EN/IEC 60529			
Ambient Air Temperature For Operation	-2555 °C without derating mounting position A < 2000 m 5570 °C with derating factor mounting position A < 2000 m			

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

# **Contractual warranty**

Warranty	18 months	



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance

	Mercury Free	
	Rohs Exemption Information	Yes
<b>⊘</b>	Pvc Free	

#### **Certifications & Standards**


Reach Regulation	REACh Declaration	
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)	
China Rohs Regulation	China RoHS declaration	
Environmental Disclosure	Product Environmental Profile	
Circularity Profile	End of Life Information	

## **ABL8MEM05040**

# **Dimensions Drawings**

#### **Regulated Switch Mode Power Supplies**

#### **Dimensions**



	a in mm	a in in.	a1 in mm	a1 in in.
ABL8MEM05040	54	2.12	42	1.65
ABL8MEM12020	54	2.12	42	1.65
ABL8MEM24003	36	1.41	24	0.94
ABL8MEM24006	36	1.41	24	0.94
ABL8MEM24012	54	2.12	42	1.65
ABL7RM24025	74	2.91	60	2.36


# **Product datasheet**

## **ABL8MEM05040**

Connections and Schema

#### Regulated Switch Mode Power Supply


#### **Internal Wiring Diagram**




#### **Regulated Switch Mode Power Supplies**

#### **Series or Parallel Connection**

**Series Connection** 



(1) Two Shottky diodes Imin = power supply In and Vmin = 50 V Parallel Connection



Family	Series	Parallel
ABL 7RM/8MEM	2 products max.	2 products max.

**NOTE:** Series or parallel connection is only recommended for products with identical references.


#### **ABL8MEM05040**

#### Performance Curves

#### **Regulated Switch Mode Power Supplies**

#### **Derating**

The ambient temperature is a determining factor that limits the power an electronic power supply can deliver continuously. If the temperature around the electronic components is too high, their life will be significantly reduced. The nominal ambient temperature for the Modular range of Phaseo power supplies is 55°C. Above this temperature, derating is necessary up to a maximum temperature of 70°C (except for the ABL7RM24025 model). The graph below shows the power as a percentage of the nominal power that the power supply can deliver continuously, depending on the ambient temperature.



X Maximum operating temperature (°C)

- (1) With an ABL7RM24025
- (2) With an ABL8MEM\*\*\*\*\*