Product datasheet

Specifications

 Green Premium[™]



regulated SMPS - 1 or 2-phase - 100..240 V AC - 24 V - 1.2 A

Local distributor code: 389706643

ABL8MEM24012

() Discontinued on: 11 Nov 2020

(!) End-of-service on: 2 Jul 2021

EAN Code: 3389119405560

Main

| Modicon Power Supply |
|--|
| Power supply |
| Regulated switch mode |
| 100240 V AC phase to phase, terminal(s): L1-L2 100240 V AC single phase, terminal(s): N-L1 120250 V DC |
| 30 W |
| 24 V DC |
| 1.2 A |
| |

Complementary

| Complementary | | | |
|---------------------------|---|--|--|
| Input Voltage Limits | 85264 V AC | | |
| Input Protection Type | Integrated fuse (not interchangeable) | | |
| Inrush Current | 20 A | | |
| Power Factor | 0.5 at 24 V DC | | |
| Efficiency | 82 % | | |
| Output Voltage Adjustment | 22.228.8 V adjustable | | |
| Power Dissipation In W | 6.6 W | | |
| Current Consumption | 0.4 A 240 V AC 0.65 A 100 V AC | | |
| Residual Ripple | 250 mV | | |
| Output Protection Type | Against short-circuits | | |
| Connections - Terminals | Screw type terminals: 2 x 0.142 x 2.5 mm ² , (AWG 26AWG 14) for input connection Screw type terminals: 4 x 0.144 x 2.5 mm ² , (AWG 26AWG 14) for output connection | | |
| Status Led | 1 LED (green) output voltage | | |
| Depth | 59 mm | | |
| Height | 100 mm | | |
| Width | 54 mm | | |
| Net Weight | 0.195 kg | | |
| Output Coupling | Parallel Series | | |

| Marking | CE |
|---------------------|---|
| Mounting Support | 35 x 7.5 mm symmetrical DIN rail panel 2 screws, diameter : 4 mm 35 x 15 mm symmetrical DIN rail |
| Operating Position | Vertical |
| Supply | SELV conforming to EN/IEC 60950-1 SELV conforming to EN/IEC 60204-1 SELV conforming to IEC 60364-4-41 |
| Dielectric Strength | 3000 V with between input and output |

Environment

| Standards | UL 508 | |
|---|--|--|
| | CSA C22.2 No 60950-1 | |
| | EN/IEC 62368-1 | |
| Product Certifications | TUV 60950-1 | |
| | EAC | |
| | RCM | |
| | KC | |
| | CCSAus | |
| | CSA 22-2 No 950 | |
| | CULus 508 | |
| Environmental Characteristic | EMC conforming to EN 55022 class B | |
| | EMC conforming to EN 61000-6-3 | |
| | EMC conforming to EN/IEC 61000-6-2 | |
| | EMC conforming to EN/IEC 61204-3 | |
| | Safety conforming to EN/IEC 60950-1 | |
| Operating Altitude | 2000 m | |
| Ip Degree Of Protection | IP20 conforming to EN/IEC 60529 | |
| Ambient Air Temperature For | -2555 °C without derating mounting position A < 2000 m | |
| Operation 5570 °C with derating factor mounting position A < 2000 m | | |

Packing Units

Unit Type Of Package 1 PCE

Number Of Units In Package 1

Contractual warranty

Warranty

18 months

1

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free
Rohs Exemption Information Yes
Pvc Free


Certifications & Standards


| Reach Regulation | REACh Declaration | |
|--------------------------|--|--|
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) | |
| China Rohs Regulation | China RoHS declaration | |
| Environmental Disclosure | Product Environmental Profile | |
| Circularity Profile | End of Life Information | |

Dimensions Drawings

Regulated Switch Mode Power Supplies

Dimensions






| | a in mm | a in in. | a1 in mm | a1 in in. |
|--------------|---------|----------|----------|-----------|
| ABL8MEM05040 | 54 | 2.12 | 42 | 1.65 |
| ABL8MEM12020 | 54 | 2.12 | 42 | 1.65 |
| ABL8MEM24003 | 36 | 1.41 | 24 | 0.94 |
| ABL8MEM24006 | 36 | 1.41 | 24 | 0.94 |
| ABL8MEM24012 | 54 | 2.12 | 42 | 1.65 |
| ABL7RM24025 | 74 | 2.91 | 60 | 2.36 |

Connections and Schema


Regulated Switch Mode Power Supply

Internal Wiring Diagram




Regulated Switch Mode Power Supplies

Series or Parallel Connection Series Connection



(1) Two Shottky diodes Imin = power supply In and Vmin = 50 V Parallel Connection



| Family | Series | Parallel |
|--------------|-----------------|-----------------|
| ABL 7RM/8MEM | 2 products max. | 2 products max. |

NOTE: Series or parallel connection is only recommended for products with identical references.

Product datasheet


ABL8MEM24012

Performance Curves

Regulated Switch Mode Power Supplies

Derating

The ambient temperature is a determining factor that limits the power an electronic power supply can deliver continuously. If the temperature around the electronic components is too high, their life will be significantly reduced. The nominal ambient temperature for the Modular range of Phaseo power supplies is 55°C. Above this temperature, derating is necessary up to a maximum temperature of 70°C (except for the ABL7RM24025 model). The graph below shows the power as a percentage of the nominal power that the power supply can deliver continuously, depending on the ambient temperature.



X Maximum operating temperature (°C) (1) With an ABL7RM24025

(2) With an ABL8MEM