Product datasheet

Specification





TeSys LRD thermal overload relays - 110...140 A - class 10A

Local distributor code:

381829625 LRD33696

EAN Code: 3389110522563

Main

Range	TeSys	
Product Name	TeSys LRD	
	TeSys Deca	
Product Or Component Type	Differential thermal overload relay	
Device Short Name	LRD	
Relay Application	Motor protection	
Product Compatibility	LC1D150	
Network Type	AC	
	DC	
Thermal Overload Class	al Overload Class Class 10A conforming to IEC 60947-4-1	
Thermal Protection Adjustment Range	otection Adjustment 110140 A	
[Ui] Rated Insulation Voltage	Power circuit: 750 V conforming to IEC 60947-4-1	
	Power circuit: 600 V conforming to CSA	
	Power circuit: 600 V conforming to UL	

Complementary

Network Frequency	0400 Hz	
Mounting Support	Plate Rail	
Tripping Threshold	1.14 +/- 0.06 Ir conforming to IEC 60947-4-1	
Auxiliary Contact Composition	1 NO + 1 NC	
th] Conventional Free Air 5 A for signalling circuit nermal Current		
Permissible Current	0.72 A at 500 V AC-15 for signalling circuit 0.06 A at 440 V DC-13 for signalling circuit	
[Ue] Rated Operational Voltage	1000 V AC 0400 Hz for power circuit conforming to IEC 60947-4-1	
Associated Fuse Rating	4 A gG for signalling circuit 4 A BS for signalling circuit	
[Uimp] Rated Impulse Withstand Voltage	nd 6 kV	
Phase Failure Sensitivity	Tripping current 130 % of Ir on two phase, the last one at 0	
Control Type	Red push-button: stop Blue push-button: reset	
Temperature Compensation	-2060 °C	

Connections - Terminals	Power circuit: screw clamp terminals 1 cable(s) 435 mm² flexible without cable end Power circuit: screw clamp terminals 1 cable(s) 435 mm² flexible with cable end Power circuit: screw clamp terminals 1 cable(s) 435 mm² solid without cable end Control circuit: screw clamp terminals 2 cable(s) 12.5 mm² flexible without cable end Control circuit: screw clamp terminals 2 cable(s) 12.5 mm² flexible with cable end Control circuit: screw clamp terminals 2 cable(s) 12.5 mm² solid without cable end
Tightening Torque	Control circuit: 1.7 N.m - on screw clamp terminals Power circuit: 9 N.m - on screw clamp terminals
Height	123 mm
Net Weight	1 kg

Environment

Climatic Withstand	conforming to IACS E10	
Ip Degree Of Protection	IP20 conforming to IEC 60529	
Ambient Air Temperature For Operation	-2060 °C without derating conforming to IEC 60947-4-1	
Ambient Air Temperature For Storage	-6070 °C	
Flame Retardance	V1 conforming to UL 94	
Mechanical Robustness	Vibrations: 6 Gn conforming to IEC 60068-2-6 Shocks: 15 Gn for 11 ms conforming to IEC 60068-2-7	
Dielectric Strength	2.2 kV at 50 Hz conforming to IEC 60947-1	
Standards	EN/IEC 60947-4-1 EN/IEC 60947-5-1 UL 60947-4-1 UL 60947-5-1 CSA C22.2 No 60947-4-1 CSA C22.2 No 60947-5-1 GB/T 14048.4 GB/T 14048.5 EN 50495	
Product Certifications	IEC UL CSA CCC EAC ATEX INERIS UKCA	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	10.2 cm
Package 1 Width	20.05 cm
Package 1 Length	13.55 cm
Package 1 Weight	1.02 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
Ø	Toxic Heavy Metal Free	
9	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information