

Product datasheet

Specifications



voltage transformer - 230..400 V - 2 x 115 V - 320 VA

Local distributor code: 389707024 ABT7PDU032G

Main

Range of product	Modicon Transformer Universal
Product or component type	Safety and isolation transformer
Rated power in VA	320 VA
Input voltage	230 V AC single phase, terminal(s): N-L1 400 V AC phase to phase, terminal(s): L1-L2
Output voltage	115/230 V AC
Secondary winding	Double
Protective cover	With
Ambient air temperature for operation	-20...60 °C

Complementary

Input voltage limits	360...440 V 207...253 V
Network frequency limits	47...63 Hz
Input voltage tolerance	+/- 15 V
Efficiency	91 %
Power dissipation in W	31.6 W
Voltage variation at nominal load	0,0286 at 230 V 0,0313 at 400 V
Output sustained overvoltage	0,014 (no load, hot state)
Maximum voltage drop at rated load	3.63 %
No load losses	15.68 W
Short-circuit voltage	0,068
Output protection type	Against overload, protection technology: external Against overvoltage, protection technology: external Against short-circuits, protection technology: external
Connections - terminals	For input connection: screw type terminals, connection capacity: 5 x 4 mm ² AWG 11 For input ground connection: screw type terminals, connection capacity: 1 x 4 mm ² AWG 11 For output connection: screw type terminals, connection capacity: 4 x 4 mm ² AWG 11
Marking	CE
Fixing mode	By 4 screws diameter: 6.5 mm on vertical panel, operating position: horizontal By 4 screws diameter: 6.5 mm on vertical panel, operating position: vertical By 4 screws diameter: 6.5 mm on horizontal panel with derating to 90 %

Output coupling	Parallel Series by internal jumper Grounding of secondary
Operating altitude	3000 m
Electrical insulation class	Class B
Status LED	1 LED (orange)input voltage
Width	123.0 mm
Height	152.0 mm
Depth	159.0 mm
Net weight	7.08 kg

Environment

Product certifications	UR EAC DNV-GL
Standards	UL 506
IP degree of protection	IP20
Environmental characteristic	EMC conforming to EN 62041 Safety conforming to EN 61558-1 Safety conforming to EN 61558-2-4
Ambient air temperature for storage	-40...80 °C
Relative humidity	0...95 % during operation
Overvoltage category	Class I conforming to VDE 0106-1
Dielectric strength	3200 V between input and ground 3200 V between output and ground 5100 V between input and output

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	7.58 kg
Package 1 Height	15.1 cm
Package 1 width	26.5 cm
Package 1 Length	27.5 cm
Unit Type of Package 2	P06
Number of Units in Package 2	24
Package 2 Weight	190.42 kg
Package 2 Height	80 cm
Package 2 width	80 cm
Package 2 Length	60 cm

Offer Sustainability


Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes

China RoHS Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
PVC free	Yes

Contractual warranty

Warranty	18 months
-----------------	-----------

Dimensions




Dimensions in mm

a	b	c	G	J	Ø
123	160	153	82	136	6.5


Dimensions in in.

a	b	c	G	J	Ø
4.84	6.30	6.02	3.23	5.35	0.25


Internal Scheme



Primary Voltage Wiring



Secondary Voltage Wiring



J2, J3, J4 Internal Jumper