# **Product datasheet**

Specification





# Standard control unit, TeSys U, 0.35-1.4A, 3P motors, magnetic protection, coil 24V DC

Local distributor code:
393517721 LUCL1XBL

EAN Code: 3389119408035

#### Main

wain	
Range	TeSys
Range Of Product	TeSys Ultra
Product Name	TeSys Ultra
Device Short Name	LUCL
Product Or Component Type	Magnetic control unit
Device Application	Motor control Motor protection
Product Specific Application	Protection of variable speed drive or soft startsoft stop unit
Main Function Available	Short-circuit protection Manual reset
Product Compatibility	Power base LUB12 Power base LUB32 Power base LUB38 Power base LUB120 Power base LUB320 Power base LUB380 Reversing contactor breaker LU2B12BL Reversing contactor breaker LU2B32BL Reversing contactor breaker LU2B38BL
[Ue] Rated Operational Voltage	690 V AC
Network Frequency	4060 Hz
Load Type	3-phase motor - cooling: self-cooled
Utilisation Category	AC-43 AC-44 AC-41
Motor Power Kw	0.25 kW at < 400415 V AC 50/60 Hz
Rated Motor Current Adjustment Range	0.351.4 A
Tripping Threshold	14.2 x lr +/- 20 %
[Uc] Control Circuit Voltage	24 V DC

#### Complementary

Control Circuit Voltage Limits	2027 V for DC circuit 24 V in operation 14.5 V for DC circuit 24 V drop-out	
Typical Current Consumption	130 mA at 24 V DC I maximum while closing with LUB12	
	220 mA at 24 V DC I maximum while closing with LUB32	
	220 mA at 24 V DC I maximum while closing with LUB38	
	60 mA at 24 V DC I rms sealed with LUB12	
	80 mA at 24 V DC I rms sealed with LUB32	
	80 mA at 24 V DC I rms sealed with LUB38	

Heat Dissipation	2 W for control circuit with LUB12
	3 W for control circuit with LUB32
	3 W for control circuit with LUB38
Operating Time	35 ms opening with LUB12 for control circuit
	35 ms opening with LUB32 for control circuit
	35 ms opening with LUB38 for control circuit
	70 ms closing with LUB12 for control circuit
	70 ms closing with LUB32 for control circuit
	70 ms closing with LUB38 for control circuit
	70 His closing with EOD36 for Control Circuit
Standards	EN 60947-6-2
	IEC 60947-6-2
	UL 60947-4-1, with phase barrier
	·
	CSA C22.2 No 60947-4-1, with phase barrier
Product Certifications	CE
	EAC
	ATEX
	ATEX
[Ui] Rated Insulation Voltage	690 V conforming to IEC 60947-6-2
	600 V conforming to UL 60947-4-1
	600 V conforming to CSA C22.2 No 60947-4-1
	000 V contonning to COA C22.2 NO 00947-4-1
[Uimp] Rated Impulse Withstand	6 kV conforming to IEC 60947-6-2
Voltage	
Safe Separation Of Circuit	400 V SELV between the control and auxiliary circuits conforming to IEC 60947-1
	400 V SELV between the control or auxiliary circuit and the main circuit conforming to
	IEC 60947-1
	120 000 11 1
Fixing Mode	Plug-in (front face)
Width	
width	45 mm
Height	66 mm
Depth	60 mm
Net Weight	0.135 kg
	0.100 kg
Compatibility Code	LUCL

### **Environment**

Ip Degree Of Protection	IP20 front panel and wired terminals conforming to IEC 60947-1
	IP20 other faces conforming to IEC 60947-1
	IP40 front panel outside connection zone conforming to IEC 60947-1
Protective Treatment	TH conforming to IEC 60068
Ambient Air Temperature For	-2570 °C
Operation	
Ambient Air Temperature For	-4085 °C
Storage	
Operating Altitude	2000 m
	2000 111
Fire Resistance	960 °C parts supporting live components conforming to IEC 60695-2-12
	650 °C conforming to IEC 60695-2-12
	000 0 00morning to 120 00000 2-12
Shock Resistance	10 gn power poles open conforming to IEC 60068-2-27
	15 gn power poles closed conforming to IEC 60068-2-27
	10 gri power poles diosed comorning to 120 00000 2 27
Vibration Resistance	2 gn, 5300 Hz, power poles open conforming to IEC 60068-2-6
	4 gn, 5300 Hz, power poles closed conforming to IEC 60068-2-6
	- g., c
Resistance To Electrostatic	8 kV level 3 in open air conforming to IEC 61000-4-2
Discharge	8 kV level 4 on contact conforming to IEC 61000-4-2
	O KV 10V61 1 011 0011ka0t 00111011111119 to 120 0 1000 1 2
Non-Dissipating Shock Wave	1 kV serial mode conforming to IEC 60947-6-2
_	2 kV common mode conforming to IEC 60947-6-2
Resistance To Radiated Fields	10 V/m 3 conforming to IEC 61000-4-3
Resistance To Fast Transients	2 kV class 3 serial link conforming to IEC 61000-4-4
	4 kV class 4 all circuits except for serial link conforming to IEC 61000-4-4
	state . a stratte except for containing contenting to 120 of 1000 4 4
Immunity To Radioelectric Fields	10 V conforming to IEC 61000-4-6

Immunity To Microbreaks	3 ms
Immunity To Voltage Dips	70 % / 500 ms conforming to IEC 61000-4-11

## **Packing Units**

•	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.3 cm
Package 1 Width	8.0 cm
Package 1 Length	10.3 cm
Package 1 Weight	125.0 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	23
Package 2 Height	15.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	3.352 kg

## **Contractual warranty**

Warranty 18 months

## Sustainability Screen Premium

**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance

<b>⊘</b>	Mercury Free
<b>②</b>	Rohs Exemption Information Yes
<b>②</b>	Pvc Free
<b>⊘</b>	Halogen Free Plastic Parts Product

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information