# **Product datasheet**

Specifications





## circuit breaker ComPact NSX100N AC/DC, 25 kA at 240 VAC, TMD trip unit 25 A, 1 pole 1d

Local distributor code: 399373037

LV438574

Discontinued on: 9 Aug 2023

() Discontinued

Important message: This product has been switched to new ComPacT range and is no longer commercialized. It will continue to be available in H1 2023 only limited to specific projects. EAN Code: 3606480073557

#### Main

Wall	
Range	ComPact
Product Name	ComPact NSX
Range Of Product	ComPact NSX100250 DC ComPact NSX100250
Device Short Name	NSX100N
Product Or Component Type	Circuit breaker
Device Application	Distribution
Number Of Poles	1P
Protected Poles Description	1t
[In] Rated Current	25 A at 40 °C
[Ue] Rated Operational Voltage	250 V DC 277 V AC 50/60 Hz
Network Type	DC AC
Network Frequency	50/60 Hz
Suitability For Isolation	Yes conforming to EN/IEC 60947-2
Utilisation Category	Category A
[Icu] Rated Ultimate Short-Circuit Breaking Capacity	50 kA Icu at 250 V DC 1P conforming to IEC 60947-2 50 kA Icu at 125 V DC 1P conforming to IEC 60947-2 25 kA Icu at 220/240 V AC 50/60 Hz conforming to IEC 60947-2
Performance Level	N 25 kA 240 V AC
Trip Unit Name	TM-D
Trip Unit Technology	Thermal-magnetic
Control Type	Toggle
Circuit Breaker Mounting Mode	Fixed

### Complementary

[Ui] Rated Insulation Voltage	750 V AC 50/60 Hz conforming to IEC 60947-2
[Uimp] Rated Impulse Withstand Voltage	8 kV conforming to IEC 60947-2

[Ics] Rated Service Short-Circuit Breaking Capacity	50 kA at 250 V DC conforming to IEC 60947-2 50 kA at 125 V DC conforming to IEC 60947-2 25 kA at 220/240 V AC 50/60 Hz conforming to IEC 60947-2
Mechanical Durability	20000 cycles
Electrical Durability	10000 cycles at 277 V In 20000 cycles at 277 V In/2
Mounting Support	Backplate
Upside Connection	Front
Downside Connection	Front
Connection Pitch	35 mm
Protection Type	for overload protection (thermal) for short-circuit protection (magnetic)
Trip Unit Rating	25 A at 40 °C
Long-Time Pick-Up Adjustment Type Ir (Thermal Protection)	Fixed
[Ir] Long-Time Protection Pick-Up Adjustment Range	1 In
[Im] Magnetic Protection Pick-Up Range	300 A
Earth-Leakage Protection	Without
Width (W)	35 mm
Height (H)	161 mm
Depth (D)	86 mm

### Environment

Standards	EN/IEC 60947
Product Certifications	CCC EAC Marine
Overvoltage Category	Class II
Electrical Shock Protection Class	Class II
Pollution Degree	3 conforming to IEC 60664-1
Ip Degree Of Protection	IP40 conforming to IEC 60529
Ik Degree Of Protection	IK07 conforming to IEC 62262
Ambient Air Temperature For Operation	-2570 °C
Ambient Air Temperature For Storage	-5085 °C
Relative Humidity	095 %
Operating Altitude	02000 m without derating 2000 m5000 m with derating

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.3 cm
Package 1 Width	13.0 cm
Package 1 Length	17.5 cm
Package 1 Weight	744.0 g

Unit Type Of Package 2	\$03
Number Of Units In Package 2	12
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	9.415 kg

### **Contractual warranty**

Warranty

18 months

### Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance



Rohs Exemption Information Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information