# **Product datasheet**

Specification





# PowerPact-circuit breaker-70A 1P AC 35kA at 480/440V(UL/IEC)-TMD-EverLink lug

BGL16070

EAN Code: 3606481193377

## Main

Range	PowerPact
Product Name	PowerPact B
Device Short Name	BG 070
Product Or Component Type	Circuit breaker
Device Application	Distribution

### Complementary

Complementary	
[In] Rated Current	70 A
Number Of Poles	1P
Protected Poles Description	1t
Control Type	Toggle
Breaking Capacity Code	G
Breaking Capacity	65 kA at 208Y/120 V AC 50/60 Hz conforming to UL 489 65 kA at 240 V AC 50/60 Hz conforming to UL 489 35 kA at 480Y/277 V AC 50/60 Hz conforming to UL 489 18 kA at 600Y/347 V AC 50/60 Hz conforming to UL 489 20 kA at 125 V DC conforming to UL 489
[Ue] Rated Operational Voltage	240 V AC 50/60 Hz conforming to UL 489
Network Frequency	50/60 Hz
[Ics] Rated Service Breaking Capacity	65 kA at 220240 V AC 50/60 Hz conforming to IEC 60947-2
[Uimp] Rated Impulse Withstand Voltage	8 kV conforming to IEC 60947-2
Trip Unit Technology	Thermal-magneticTM-D,
Continuous Current Rating	80 %
[Ui] Rated Insulation Voltage	800 V conforming to IEC 60947-2
Trip Unit Name	TM-D
Suitability For Isolation	Yes conforming to IEC 60947-2
Utilisation Category	Category A
Mechanical Durability	15000 cycles conforming to IEC 947-1 Annex F ed 5.2
Electrical Durability	10000 cycles conforming to IEC 947-1 Annex K ed 5.2 In
Connection Pitch	27 mm
Awg Gauge	AWG 6AWG 2/0 fine stranded aluminium/copper AWG 14AWG 3/0 rigid or stranded aluminium/copper
Mounting Mode	Clip-on (35 mm symmetrical DIN rail) By screws (plate)

<b>Electrical Connection</b>	Everlink lug, line Everlink lug, load
Tightening Torque	5 N.m for 2.516 mm² (AWG 14AWG 4) 9 N.m for 2595 mm² (AWG 3AWG 3/0)
Power Wire Stripping Length	20 mm
Color	Grey (RAL 7016)
9 Mm Pitches	3
Height	137 mm
Width	27 mm
Depth	80 mm
Net Weight	0.51 kg
Quantity Per Set	Set of 1
Circuit Breaker Application	HACR rated

## **Environment**

Quality Labels	CE
Standards	EN/IEC 60947-2 EN/IEC 60947-5-1 GB 14048.2 UL 489 NMX J-266 NEMA AB1 CSA C22.2 No 5
Product Certifications	UL IEC CCC EAC CSA NOM
Ip Degree Of Protection	Front cover: IP40 conforming to IEC 60529
Ik Degree Of Protection	IK07 conforming to IEC 62262
Pollution Degree	3 conforming to IEC 60947-1
Ambient Air Temperature For Operation	-2570 °C
Ambient Air Temperature For Storage	-5085 °C
Operating Altitude	2000 m without derating 5000 m with derating

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.556 cm
Package 1 Width	11.938 cm
Package 1 Length	19.05 cm
Package 1 Weight	453.592 g

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance

<b>②</b>	Mercury Free	
<b>②</b>	Rohs Exemption Information	Yes
<b>②</b>	Pvc Free	
<b>⊘</b>	Halogen Free Product	

### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations