Product datasheet

Specifications





Spacial SF 1 entry cable gland plate - fixed by clips - 700x600 mm

NSYEC761

EAN Code: 3606480211492

Main

Range	Spacial
Product Or Component Type	Cable gland plate
Accessory / Separate Part Category	Cable management accessory
Application	Prisma application Multi-purpose
Range Compatibility	Spacial Spacial SF Spacial Spacial SFP
Mounting Location	Enclosure bottom
Cable Gland Type	Standard
Cable Entry	1 entry
Device Composition	fixing elements 1 plate polyurethane adhesive gasket with cross-section of 15 x 25 mm
Quantity Per Set	Set of 1
Material	Galvanised steel

Complementary

Width	700 mm nominal: 516 mm useful:
Depth	600 mm nominal:
Thickness	1.5 mm

Packing Units

V	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.0 cm
Package 1 Width	34.5 cm
Package 1 Length	55.0 cm
Package 1 Weight	3.898 kg
Unit Type Of Package 2	РАМ
Number Of Units In Package 2	40
Package 2 Height	45.0 cm
Package 2 Width	100.0 cm
Package 2 Length	120.0 cm

Package 2 Weight

169.0 kg

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations