

# Product datasheet

Specifications



## C60HC3P63ACBSEN

C60HC363

 **Discontinued on:** 15 Dec 2020

 **Discontinued**

### Main

Device Application	Distribution
Range	Multi9
Product Name	C60
Product Or Component Type	Miniature circuit-breaker
Device Short Name	C60H
Poles Description	3P
Number Of Protected Poles	3
Trip Unit Technology	Thermal-magnetic
Curve Code	C

### Complementary

[In] Rated Current	63 A
Breaking Capacity	10 kA Icu at 440 V AC 50/60 Hz conforming to EN/IEC 60947-2 15 kA Icu at 400...415 V AC 50/60 Hz conforming to EN/IEC 60947-2 10000 A Icn at 230/400 V AC 50/60 Hz conforming to EN 60898 25 kA Icu at 125 V DC 2P conforming to EN/IEC 60947-2 30 kA Icu at 230...240 V AC 50/60 Hz conforming to EN/IEC 60947-2 40 kA Icu at 125 V DC 3P conforming to EN/IEC 60947-2 50 kA Icu at <= 250 V DC 4P conforming to EN/IEC 60947-2

### Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

# Sustainability

**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Eu Rohs Directive	Not applicable, out of EU RoHS legal scope
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins