Product datasheet

Specification





Fuse carrier TeSys DF, 1P+N 32A, fuse size 10 x 38 mm

Local distributor code: 393394070

DF101N

EAN Code: 3389119407229

Main

mann		
Range	TeSys	
Product Name	TeSys DF	
Product Or Component Type	Fuse carrier	
Device Short Name	DF10	
Device Composition	tubular link for locked in Neutral pole	
Product Compatibility	DF2CA fuse cartridge DF2CN fuse cartridge	
Poles Description	1P + N	
Fuse Size	e 10 x 38 mm	
Fuse Type	, aM , gG	
Control Type	Toggle padlockable	
Utilisation Category	AC-20B conforming to IEC 60947-3 DC-20B conforming to IEC 60947-3	
[Ue] Rated Operational Voltage	690 V AC 690 V DC	
[le] Rated Operational Current	32 A at 400 V AC	
[Ith] Conventional Free Air Thermal Current	32 A 20 °C	
[Ui] Rated Insulation Voltage	690 V AC	
[Uimp] Rated Impulse Withstand Voltage	6 kV	
Overvoltage Category	III	
Short-Circuit Withstand	120 kA 400 V conforming to IEC 60947-3 120 kA 500 V conforming to IEC 60947-3	
Power Dissipation In W	3 W maximum power dissipation by fuse	

Complementary

Standards	EN/IEC 60947-3 EN/IEC 60269-2 UL 4248-1 CSA C22.2 No 4248-1 EN 45545-2: R22 HL2
Product Certifications	IEC UL recognized
	CSA
	CCC
	EAC
	DNV-GL
Mounting Support	35 mm symmetrical DIN rail

10 May 2024 Life Is On Schneider

Mounting Position	Vertical (tolerance: +/- 23°)	
Connections - Terminals	Screw clamp terminals 1 cable(s) 116 mm²rigid Screw clamp terminals 2 cable(s) 16 mm²rigid Screw clamp terminals 1 cable(s) 116 mm²flexible with or without Screw clamp terminals 2 cable(s) 16 mm²flexible with or without	
Tightening Torque	2.2 N.m - with screwdriver PZ2 2.2 N.m - with screwdriver flat Ø 5.5 mm	
Height	79.5 mm	
Width	35 mm	
Depth	61 mm	
Net Weight	0.087 kg	
Quantity Per Set Set of 6		

Environment

Ambient Air Temperature For Storage	-4070 °C
Ambient Air Temperature For Operation	-4070 °C with derating above 20°C
Operating Altitude	02000 m
Ip Degree Of Protection	IP20
Pollution Degree	3
Fire Resistance	960 °C conforming to IEC 60695-2-1
Compatibility Code	DF10

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.5 cm
Package 1 Width	6.2 cm
Package 1 Length	8 cm
Package 1 Weight	92 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	6
Package 2 Height	6.8 cm
Package 2 Width	8.5 cm
Package 2 Length	22.2 cm
Package 2 Weight	584 g
Unit Type Of Package 3	S03
Number Of Units In Package 3	96
Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	9.885 kg

Contractual warranty

Warranty

10 May 2024

18 months

Sustainability Green Premium

Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

②	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations Circularity Profile