# **Product datasheet**

Specification





# Modular liquid level control relay, 5 A, 1 CO, 24...240 V AC/DC

Local distributor code: 389834942

RM35LV14MW

EAN Code: 3389119405249

## Main

Range Of Product	Harmony Control Relays
Relay Type	Level control relay
Product Or Component Type	Level control relay
Relay Name	RM35L
Relay Monitored Parameters	Detection by discrete sensors
Time Delay	Adjustable 0.15 s, +/- 10 % Tt- time delay upon fault
Switching Capacity In Va	1250 VA
Minimum Switching Current	10 mA at 5 V DC
Maximum Switching Current	5 A AC/DC
Power Consumption	5 VA AC
Utilisation Category	AC-12 conforming to IEC 60947-5-1 AC-13 conforming to IEC 60947-5-1 AC-14 conforming to IEC 60947-5-1 AC-15 conforming to IEC 60947-5-1 DC-12 conforming to IEC 60947-5-1 DC-13 conforming to IEC 60947-5-1
Contacts Type And Composition	2 C/O

# Complementary

Reset Time	1000 ms 4000 ms
Maximum Switching Voltage	250 V AC/DC
[Un] Rated Nominal Voltage	24240 V AC/DC 50/60 Hz, non self-powered
Supply Voltage Limits	20.4264 V AC/DC
Operating Voltage Tolerance	- 15 % + 10 % Un
Power Consumption	1.5 W DC
Output Contacts	1 C/O
Nominal Output Current	5 A
Delay At Power Up	0.5 s
Measurement Accuracy	+/- 10 % of the full scale value +/- 20 % for the HS range
Repeat Accuracy	+/- 2 % for time delay
Measurement Error	0.5 %/°C with temperature variation
Sensitivity Adjustment	5100 %

Maximum Supply Current For Sensors	40 mA
Cable Capacitance	10 nF for probe cable
<b>V</b> arking	CE : EMC 89/336/EEC CE : 73/23/EEC
Overvoltage Category	III conforming to IEC 60664-1
Insulation Resistance	> 500 MOhm at 500 V DC between supply and relay output conforming to IEC 60255-5 > 500 MOhm at 500 V DC between measurement and relay output conforming to IEC 60664-1 > 1 MOhm at 500 V DC between supply and measurement conforming to IEC 60255-5 > 500 MOhm at 500 V DC between supply and relay output conforming to IEC 60664-1 > 500 MOhm at 500 V DC between measurement and relay output conforming to IEC
	60255-5 > 1 MOhm at 500 V DC between supply and measurement conforming to IEC 60664-1
[Ui] Rated Insulation Voltage	250 V conforming to IEC 60664-1
Operating Position	Any position without derating
Connections - Terminals	Screw terminals, 1 x 0.51 x 4 mm² (AWG 20AWG 11) solid without cable end Screw terminals, 2 x 0.52 x 2.5 mm² (AWG 20AWG 14) solid without cable end Screw terminals, 2 x 0.22 x 1.5 mm² (AWG 24AWG 16) flexible with cable end Screw terminals, 1 x 0.21 x 2.5 mm² (AWG 24AWG 12) flexible with cable end
Tightening Torque	0.61 N.m conforming to IEC 60947-1
Housing Material	Self-extinguishing plastic
Local Signalling	LED (yellow) for relay ON LED (green) for power ON LED (yellow) for timer ON
Mounting Support	35 mm symmetrical DIN rail conforming to IEC 60715
Electrical Durability	100000 cycles
Mechanical Durability	30000000 cycles
Operating Rate	<= 360 operations/hour full load
Safety Reliability Data	B10d = 170000 MTTFd = 182.6 years
Width	35 mm
Control Type	Without test button
Environment	
mmunity To Microbreaks	100 ms DC 90 ms AC
Electromagnetic Compatibility	Emission standard for industrial environments conforming to IEC 61000-6-4 Emission standard for residential, commercial and light-industrial environments conforming to IEC 61000-6-3 Immunity for industrial environments conforming to NF EN/IEC 61000-6-2

Immunity To Microbreaks	100 ms DC 90 ms AC
Electromagnetic Compatibility	Emission standard for industrial environments conforming to IEC 61000-6-4 Emission standard for residential, commercial and light-industrial environments conforming to IEC 61000-6-3 Immunity for industrial environments conforming to NF EN/IEC 61000-6-2
Standards	IEC 60255-6
Product Certifications	GOST CSA UL GL C-Tick
Ambient Air Temperature For Storage	-4070 °C
Ambient Air Temperature For Operation	-2050 °C
Relative Humidity	95 % at 55 °C conforming to IEC 60068-2-30

Ip Degree Of Protection	IP20 (terminals) conforming to IEC 60529 IP30 (casing) conforming to IEC 60529
Pollution Degree	3 conforming to IEC 60664-1
Dielectric Test Voltage	2 kV, 1 min AC 50 Hz conforming to IEC 60255-5 2 kV, 1 min AC 50 Hz conforming to IEC 60664-1

# **Packing Units**

•	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.8 cm
Package 1 Width	8 cm
Package 1 Length	9.7 cm
Package 1 Weight	133 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	48
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	7.131 kg

# **Contractual warranty**

Warranty 18 months

# Sustainability Green Premium

**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance



Mercury Free



Rohs Exemption Information

Yes

## **Certifications & Standards**


Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information


## RM35LV14MW

## **Dimensions Drawings**

## **Level Control Relays**

## **Dimensions and Mounting**






## **Product datasheet**

## RM35LV14MW

Connections and Schema

## Level Control Relays

## Wiring Diagram




## **Technical Description**

## **Function Diagrams**

#### **Control of Two Levels**

Fill/Empty function



#### Legend

Un Nominal supply voltage


(1) Min. level(2) Max. level

11-12/11-14, 21-22/21-24 Output relay connections


Relay status: black color = energized.

#### Control of One Level


Empty function T on



#### Empty function T off




#### Fill function T on



Fill function T off

## **Product datasheet**

## RM35LV14MW



#### Legend

**Tt** Time delay after crossing of threshold **Un** Supply voltage

(1) Level threshold

11-12/11-14, 21-22/21-24 Output relay connections

Relay status: black color = energized.