Product datasheet

Specification





Fuse carrier TeSys DF, 3P 32A, fuse size 10x38 mm, blown fuse indicator

DF103V

EAN Code: 3389119407328

Main

Range	TeSys
Product Name	TeSys DF
Product Or Component Type	Fuse carrier
Device Short Name	DF10
Product Compatibility	DF2CA fuse cartridge DF2CN fuse cartridge
Poles Description	3P
Fuse Size	10 x 38 mm
Fuse Type	, aM , gG
Control Type	Toggle padlockable
Local Signalling	Blown fuse indication
Utilisation Category	AC-20B conforming to IEC 60947-3 DC-20B conforming to IEC 60947-3
[Ue] Rated Operational Voltage	690 V AC 690 V DC
[le] Rated Operational Current	32 A at 400 V AC
[Ith] Conventional Free Air Thermal Current	32 A 20 °C
[Ui] Rated Insulation Voltage	690 V AC
[Uimp] Rated Impulse Withstand Voltage	6 kV
Overvoltage Category	III
Short-Circuit Withstand	120 kA 400 V conforming to IEC 60947-3 120 kA 500 V conforming to IEC 60947-3
Power Dissipation In W	3 W maximum power dissipation by fuse

Complementary

Mounting Support	35 mm symmetrical DIN rail
	DNV-GL
	EAC
	CCC
	CSA
	UL recognized
Product Certifications	IEC
	EN 45545-2: R22 HL2
	CSA C22.2 No 4248-1
	UL 4248-1
	EN/IEC 60269-2
Standards	EN/IEC 60947-3

23 Apr 2024 Life Is On Schneider

Mounting Position	Vertical (tolerance: +/- 23°)	
Connections - Terminals	Screw clamp terminals 1 cable(s) 116 mm²rigid	
	Screw clamp terminals 2 cable(s) 16 mm²rigid	
	Screw clamp terminals 1 cable(s) 116 mm²flexible with or without	
	Screw clamp terminals 2 cable(s) 16 mm²flexible with or without	
Tightening Torque	2.2 N.m - with screwdriver PZ2	
	2.2 N.m - with screwdriver flat Ø 5.5 mm	
Height	79.5 mm	
Width	52.5 mm	
Depth	61 mm	
Net Weight	0.126 kg	
Quantity Per Set	Set of 4	

Environment

Ambient Air Temperature For Storage	-4070 °C
Ambient Air Temperature For Operation	-4070 °C with derating above 20°C
Operating Altitude	02000 m
Ip Degree Of Protection	IP20
Pollution Degree	3
Fire Resistance	960 °C conforming to IEC 60695-2-1
Compatibility Code	DF10

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.2 cm
Package 1 Width	6.2 cm
Package 1 Length	8 cm
Package 1 Weight	135 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	4
Package 2 Height	6.7 cm
Package 2 Width	8.5 cm
Package 2 Length	22.2 cm
Package 2 Weight	574 g
Unit Type Of Package 3	S03
Number Of Units In Package 3	64
Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	9.758 kg

Contractual warranty

Warranty

18 months

Sustainability Green Premium

Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations
	Circularity Profile