

Product datasheet

Specifications



Acti9 iKQ 1P 40A B Miniature Circuit breaker

Local distributor code:

396734349

SE10B140

EAN Code: 5018934965895

Main

Range	Acti9
Product Name	iKQ
Product Or Component Type	Miniature circuit-breaker
Poles Description	1P
Number Of Protected Poles	1
[In] Rated Current	40 A
Network Type	AC
Trip Unit Technology	Thermal-magnetic
Curve Code	B
Breaking Capacity	10000 A Icn at 240 V AC 50/60 Hz conforming to EN 60898-1

Complementary

Network Frequency	50/60 Hz
[Ue] Rated Operational Voltage	240 V AC 50/60 Hz
Magnetic Tripping Limit	3...5 x In
[Ics] Rated Service Breaking Capacity	7500 A conforming to EN 60898-1 - 240 V AC 50/60 Hz
Limitation Class	3 conforming to EN/IEC 60898-1
[Uij] Rated Insulation Voltage	440 V AC 50/60 Hz conforming to EN/IEC 60898-1
[Uimp] Rated Impulse Withstand Voltage	4 kV conforming to EN/IEC 60898-1
Contact Position Indicator	Yes
Control Type	Toggle
Local Signalling	Trip indicator
Mounting Mode	Plug-on
Mounting Support	Rail
9 Mm Pitches	2
Height	85 mm
Width	18 mm
Depth	78.5 mm
Net Weight	0.121 kg
Colour	White
Mechanical Durability	20000 cycles

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Electrical Durability	10000 cycles
Connections - Terminals	Single terminal (bottom) 1...35 mm² rigid Single terminal (bottom) 1...25 mm² flexible
Wire Stripping Length	14 mm for bottom connection
Tightening Torque	2 N.m bottom
Earth-Leakage Protection	Without

Environment

Standards	EN/IEC 60898-1
Ip Degree Of Protection	IP20 conforming to IEC 60529
Pollution Degree	2 conforming to EN/IEC 60898-1
Overvoltage Category	III

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.8 cm
Package 1 Width	8.2 cm
Package 1 Length	9.5 cm
Package 1 Weight	132 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	12
Package 2 Height	9.7 cm
Package 2 Width	10.2 cm
Package 2 Length	24 cm
Package 2 Weight	1.666 kg
Unit Type Of Package 3	S03
Number Of Units In Package 3	96
Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	12.71 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

 Mercury Free	
 Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins