

Product datasheet

Specifications



Easy UPS 3S 10 kVA 400 V 3:3 UPS for internal batteries

Local distributor code:
422503538

E3SUPS10KHB

Overview

Presentation	High-efficiency 3-phase UPS that features advanced product features, competitive specifications, and robust electrical design, making business continuity easy in the data center or electrical room. This is an exceptionally easy to install, operate, maintain, and service 10 kVA UPS, ideal for small and medium businesses. Includes dust filter and conformance-coated boards for harsh environments. This UPS is for internal batteries, but is supplied without batteries, so you can easily customize the battery runtime. For battery runtime details, see the runtime charts published under the Documents tab.
Lead Time	Usually Ships within 6 Weeks

Main

Main Input Voltage	400 V 3 phases
Other Input Voltage	380 V 415 V
Main Output Voltage	400 V 3 phases
Other Output Voltage	380 V 415 V
Rated Power In W	10 kW
Rated Power In Va	10 kVA
Provided Equipment	Dust filter Installation guide

Batteries & Runtime

Efficiency	View Efficiency Graph
Battery Type	VRLA
Battery Voltage	240 V
Maximum Short-Circuit Current	10 kA
Number Of Battery Filled Slots	0
Number Of Battery Free Slots	3
Discharge Battery Voltage	+/- 198 V DC

Physical

Colour	White (RAL 9003)
Height	140 cm
Width	38 cm
Depth	92.8 cm
Net Weight	112 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Usb Compatible	Yes
----------------	-----

Input

Maximum Input Current	18 A
Input Harmonic Distortion	Less than 3 % for full load
Load Power Factor	0.9 leading to 0.9 lagging
Input Power Factor At Full Load	0.99
Input Voltage Limits	304...477 V
Network Frequency	45...65 Hz

Output

Maximum Configurable Power In Va	10 kVA
Maximum Configurable Power In W	10 kW
Output Frequency	50 Hz sync to mains 60 Hz sync to mains
Harmonic Distortion	Less than 3 %
Output Harmonic Distortion	< 3% linear load
Output Overload Operation	130-150% for 1 minute and 125-130% for 10 minutes
Output Voltage Tolerance	+/- 1.5 %
Ups Type	Double conversion online

Conformance

Product Certifications	CE EAC RCM
------------------------	------------------

Environmental

Ambient Air Temperature For Operation	0...40 °C
Relative Humidity	0...95 % non-condensing
Operating Altitude	0...3333 ft
Ambient Air Temperature For Storage	-15...40 °C
Storage Relative Humidity	0...95 % non-condensing
Storage Altitude	0.00...15240.00 m
Acoustic Level	60 dBA
Heat Dissipation	516 W
Ip Degree Of Protection	IP20

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	164 cm
Package 1 Width	101.4 cm
Package 1 Length	56.3 cm

Package 1 Weight	145 kg
------------------	--------

Contractual warranty

Warranty	1 year on-site repair or replace with factory authorized Start-Up
----------	---

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.


[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

 Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information