Product datasheet

Specifications





Lisse - Shaver Socket - 2 gang - 115/230V Satin Brass with Black Interior

Local distributor code: 404918646

GGBL7090BSBS

EAN Code: 3606481260147

Main

Range	Lisse
Aesthetic Name	Screwless deco
Product Or Component Type	Shaver socket
Colour Tint	Interior: black Cover plate: satin brass
Type Of Packing	Bag

Complementary

Device Mounting	Wall mounted
Input Voltage	230 V AC 50 Hz
Output Voltage	115230 V
Material	Stainless steel
Fixing Mode	Concealed screws
Connections - Terminals	Screw terminals
Type Of Installation	Indoor
Width	87 mm
Height	148 mm
Depth	51 mm
Net Weight	0.708 kg

Environment

Standards	BS EN 61558-2-5
Ip Degree Of Protection	IP20

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.500 cm
Package 1 Width	12.000 cm
Package 1 Length	18.000 cm
Package 1 Weight	802.900 g
Unit Type Of Package 2	CAR

Number Of Units In Package 2	25
Package 2 Height	20.500 cm
Package 2 Width	45.500 cm
Package 2 Length	63.000 cm
Package 2 Weight	20.821 kg
Unit Type Of Package 3	PAM
Number Of Units In Package 3	300
Package 3 Height	98.500 cm
Package 3 Width	120.000 cm
Package 3 Length	100.000 cm
Package 3 Weight	269.846 kg

Contractual warranty

Warranty 18 months



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO2 products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Rohs Exemption Information

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations