Product datasheet

Specification





Motor circuit breaker, TeSys GV2, 3P, 17-23 A, thermal magnetic, screw clamp terminals

Local distributor code: 386421138 GV2RT21

EAN Code: 3389110520729

Main

Range	TeSys Deca	
Product Name	TeSys GV2 TeSys Deca	
Product Or Component Type	Motor circuit breaker	
Device Short Name	GV2RT	
Device Application	Motor protection	
Trip Unit Technology	Thermal-magnetic	

Complementary

Complementary	
Poles Description	3P
Network Type	AC
Utilisation Category	Category A conforming to IEC 60947-2 AC-3 conforming to IEC 60947-4-1 AC-3e conforming to IEC 60947-4-1
Network Frequency	50/60 Hz conforming to IEC 60947-4-1
Fixing Mode	35 mm symmetrical DIN rail: clipped Panel: screwed (with adaptor plate)
Motor Power Kw	5.5 kW at 220/230 V AC 50/60 Hz motor protection high peak current 9 kW at 400/415 V AC 50/60 Hz motor protection high peak current 11 kW at 400/415 V AC 50/60 Hz motor protection high peak current 11 kW at 440 V AC 50/60 Hz motor protection high peak current 11 kW at 500 V AC 50/60 Hz motor protection high peak current 18.5 kW at 690 V AC 50/60 Hz motor protection high peak current
Breaking Capacity	50 kA Icu at 220/230 V AC 50/60 Hz conforming to IEC 60947-2 15 kA Icu at 400/415 V AC 50/60 Hz conforming to IEC 60947-2 6 kA Icu at 440 V AC 50/60 Hz conforming to IEC 60947-2 4 kA Icu at 500 V AC 50/60 Hz conforming to IEC 60947-2 3 kA Icu at 690 V AC 50/60 Hz conforming to IEC 60947-2
Control Type	Toggle
[In] Rated Current	23 A
Thermal Protection Adjustment Range	1723 A conforming to IEC 60947-4-1
Magnetic Tripping Current	400 A
[Ith] Conventional Free Air Thermal Current	23 A conforming to IEC 60947-4-1
[Ue] Rated Operational Voltage	690 V AC 50/60 Hz conforming to IEC 60947-2
[Ui] Rated Insulation Voltage	690 V AC 50/60 Hz conforming to IEC 60947-2
[Uimp] Rated Impulse Withstand Voltage	6 kV conforming to IEC 60947-2
Suitability For Isolation	Yes conforming to IEC 60947-1 § 7-1-6

Power Dissipation Per Pole	2.5 W	
Mechanical Durability	100000 cycles	
Electrical Durability	100000 cycles for AC-3 at 415 V In 100000 cycles for AC-3e at 415 V In	
Rated Duty	Continuous conforming to IEC 60947-4-1	
Tightening Torque	1.7 N.m - on screw clamp terminal	
Width	45 mm	
Height	89 mm	
Depth	78.5 mm	

Environment

Standards	EN/IEC 60947-2 EN/IEC 60947-4-1	
Product Certifications	CCC UL CSA EAC LROS (Lloyds register of shipping) BV UKCA	
Ik Degree Of Protection	IK04	
Ip Degree Of Protection	IP20 conforming to IEC 60529	
Climatic Withstand	conforming to IACS E10	
Ambient Air Temperature For Storage	-4080 °C	
Fire Resistance	960 °C conforming to IEC 60695-2-11	
Ambient Air Temperature For Operation	-2060 °C	
Mechanical Robustness	Shocks: 30 Gn for 11 ms Vibrations: 5 Gn, 5150 Hz	
Operating Altitude	2000 m	

Packing Units

•	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.600 cm
Package 1 Width	9.300 cm
Package 1 Length	4.800 cm
Package 1 Weight	290.000 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	24
Package 2 Height	15.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	7.169 kg
Unit Type Of Package 3	P06
Number Of Units In Package 3	288

Package 3 Height	75.000 cm	
Package 3 Width	60.000 cm	
Package 3 Length	80.000 cm	
Package 3 Weight	97.480 ka	

Contractual warranty

Warranty 18 months

Sustainability Green Premium

Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes


Certifications & Standards


Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information

Dimensions Drawings

GV2RT


Dimensions







X1: Electrical clearance = 40 mm for Ue < 690 V **Mounting**

Mounting of external operator GV2AP03











c = 80 on AM1 DP200 (35 x 7.5) c = 88 on AM1 DE200, ED200 (35 x 15) On panel with adapter plate GV2AF02




On pre-slotted plate AM1 PA



On rails DZ5 MB

Product datasheet

GV2RT21



Connections and Schema

GV2ME•• and GV2RT

