Product datasheet

Specifications





TeSys GV2 - safety undervoltage trip - 380...400V AC 50Hz

Local distributor code: 381798963

GVAX385

EAN Code: 3389110346312

Main

Range	TeSys TeSys Deca
Product Or Component Type	Safety undervoltage trip
Device Short Name	GVAX

Complementary

Complementary	
Range Compatibility	TeSys GV2ME TeSys Deca
[Uc] Control Circuit Voltage	380400 V AC 50 Hz 440 V AC 60 Hz
Control Circuit Voltage Limits	0.851.1 Un
[Ui] Rated Insulation Voltage	690 V AC conforming to IEC 60947-1 600 V AC conforming to UL 60947-4-1 600 V AC conforming to CSA C22.2 No 60947-4-1
Threshold Tripping Voltage	0.70.35 Un
Inrush Power In Va	12 VA AC
Inrush Power In W	8 W
Hold-In Power Consumption In Va	3.5 VA AC
Hold-In Power Consumption In W	1.1 W
Operating Time	1015 ms conforming to IEC 60947-1
On-Load Factor	100 %
Connections - Terminals	Screw clamp terminals 1 cable(s) 12.5 mm ² solid Screw clamp terminals 2 cable(s) 12.5 mm ² solid Screw clamp terminals 1 cable(s) 0.752.5 mm ² flexible without cable end Screw clamp terminals 2 cable(s) 0.752.5 mm ² flexible without cable end Screw clamp terminals 1 cable(s) 0.751.5 mm ² flexible with cable end Screw clamp terminals 2 cable(s) 0.751.5 mm ² flexible with cable end
Tightening Torque	< 1.4 N.m on screw clamp terminals
Mechanical Durability	30000 cycles
Quantity Per Set	Set of 10
Height	89 mm
Width	18 mm
Depth	66 mm
Net Weight	0.105 kg
Colour	Dark grey

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.800 cm
Package 1 Width	8.500 cm
Package 1 Length	9.500 cm
Package 1 Weight	120.000 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	42
Package 2 Height	15.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	5.424 kg

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information

Product datasheet

Connections and Schema

GVAX •••

