

Product datasheet

Specifications



module XPSBC - two-hand control - 24 V AC

XPSBC3110

EAN Code: 3389110766868

❗ Discontinued

Main

Range Of Product	Preventa Safety automation
Product Or Component Type	Preventa safety module
Safety Module Name	XPSBC
Safety Module Application	For electrical monitoring of two-hand control stations
Function Of Module	Monitoring two-hand control station
Safety Level	Can reach PL e/category 4 conforming to EN/ISO 13849-1
Safety Reliability Data	MTTFd = 63.9 years conforming to EN/ISO 13849-1 DC > 99 % conforming to EN/ISO 13849-1 PFHd = 1.75E-8 1/h conforming to EN/IEC 62061
Connections - Terminals	Captive screw clamp terminals, 1 x 0.14...1 x 2.5 mm² flexible without cable end Captive screw clamp terminals, 1 x 0.14...1 x 2.5 mm² solid without cable end Captive screw clamp terminals, 1 x 0.25...1 x 1.5 mm² flexible with cable end, with bezel Captive screw clamp terminals, 1 x 0.25...1 x 2.5 mm² flexible with cable end, without bezel Captive screw clamp terminals, 2 x 0.14...2 x 0.75 mm² flexible without cable end Captive screw clamp terminals, 2 x 0.14...2 x 0.75 mm² solid without cable end Captive screw clamp terminals, 2 x 0.25...2 x 1 mm² flexible with cable end, without bezel Captive screw clamp terminals, 2 x 0.5...2 x 1.5 mm² flexible with cable end, with double bezel
Output Type	Relay, 2 NO circuit(s), volt-free
Number Of Additional Circuits	1 NC
[Us] Rated Supply Voltage	24 V AC - 15...10 %

Complementary

Synchronisation Time Between Inputs	0.5 s
Supply Frequency	50/60 Hz
Power Consumption In Va	6 VA
Input Protection Type	Internal, electronic
Number Of Inputs	1 NC + NO
Input Voltage	30 V
Input Current	50 mA
Input Compatibility	Two-hand control conforming to EN 574/ISO 13851-III C
[Uc] Control Circuit Voltage	48 V DC
Breaking Capacity	180 VA holding AC-15 C300 relay output 1800 VA inrush AC-15 C300 relay output

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Breaking Capacity	1.5 A at 24 V (DC-13) time constant: 50 ms for relay output
[Ith] Conventional Free Air Thermal Current	2.5 A
Associated Fuse Rating	4 A gG for relay output conforming to EN/IEC 60947-5-1, DIN VDE 0660 part 200
Minimum Output Current	10 mA for relay output
Minimum Output Voltage	17 V for relay output
Maximum Response Time On Input Open	30 ms
[Ui] Rated Insulation Voltage	300 V (pollution degree 2) conforming to IEC 60947-5-1 300 V (pollution degree 2) conforming to DIN VDE 0110 part 1
[Uimp] Rated Impulse Withstand Voltage	4 kV overvoltage category III conforming to IEC 60947-5-1 4 kV overvoltage category III conforming to DIN VDE 0110 part 1
Local Signalling	3 LEDs
Mounting Support	35 mm symmetrical DIN rail
Net Weight	0.4 kg

Environment

Standards	EN/IEC 60204-1 EN 574 type III C/ISO 13851 EN/IEC 60947-5-1
Product Certifications	CSA UL TÜV
Ip Degree Of Protection	IP20 (terminals) conforming to EN/IEC 60529 IP40 (enclosure) conforming to EN/IEC 60529
Ambient Air Temperature For Operation	-10...55 °C
Ambient Air Temperature For Storage	-25...85 °C

Contractual warranty

Warranty	18 months
----------	-----------