Product datasheet

Main





module XPSDM - 6 coded magnetic switch - 24 V DC

Local distributor code: 407169557

XPSDME1132P

! Discontinued on: 3 Jul 2021

EAN Code: 3389110274172

! Discontinued

Range Of Product	Preventa Safety automation	
Product Or Component Type	Preventa safety module	
Safety Module Name	XPSDME	
Safety Module Application	Monitoring 6 coded magnetic switches	
Function Of Module	Coded magnetic switch monitoring	
Safety Level	Can reach PL e/category 4 conforming to EN/ISO 13849-1 Can reach SILCL 3 conforming to EN/IEC 62061	
Safety Reliability Data	DC > 99 % conforming to EN/ISO 13849-1 MTTFd = 82.4 years conforming to EN/ISO 13849-1 PFHd = 3.97E-9 1/h conforming to EN/IEC 62061	
[Us] Rated Supply Voltage	24 V DC - 2020 %	
Output Type	Relay, 2 NO circuit(s), volt-free	

2 solid state outputs

Complementary

Number Of Additional Circuits

J	
Synchronisation Time Between Inputs	< 0.5 s
Power Consumption In W	3.5 W
Input Protection Type	Internal, electronic
[Uc] Control Circuit Voltage	28 V DC
Maximum Line Resistance	100 Ohm
Breaking Capacity	180 VA holding AC-15 C300 relay output 1800 VA inrush AC-15 C300 relay output
Breaking Capacity	1.5 A at 24 V (DC-13) time constant: 50 ms for relay output
Output Thermal Current	6 A per relay for relay output
[Ith] Conventional Free Air Thermal Current	12 A
Associated Fuse Rating	4 A gG for relay output conforming to EN/IEC 60947-5-1, DIN VDE 0660 part 200 6 A fast blow for relay output conforming to EN/IEC 60947-5-1, DIN VDE 0660 part 200
Minimum Output Current	10 mA for relay output
Minimum Output Voltage	17 V for relay output
Maximum Response Time On Input Open	20 ms
[Ui] Rated Insulation Voltage	300 V (pollution degree 2) conforming to IEC 60947-5-1 300 V (pollution degree 2) conforming to DIN VDE 0110 part 1

Life Is On Schneider 26 Apr 2024

[Uimp] Rated Impulse Withstand Voltage	4 kV overvoltage category III conforming to IEC 60947-5-1 4 kV overvoltage category III conforming to DIN VDE 0110 part 1
Local Signalling	15 LEDs
Connections - Terminals	Captive screw clamp terminals, removable terminal block, 1 x 0.21 x 2.5 mm ² flexible without cable end
	Captive screw clamp terminals, removable terminal block, 1 x 0.21 x 2.5 mm ² solid without cable end
	Captive screw clamp terminals, removable terminal block, 1 x 0.251 x 2.5 mm ² flexible with cable end, with bezel
	Captive screw clamp terminals, removable terminal block, 1 x $0.251 \times 2.5 \text{ mm}^2$ flexible with cable end, without bezel
	Captive screw clamp terminals, removable terminal block, 2 x 0.22 x 1 mm² solid without cable end
	Captive screw clamp terminals, removable terminal block, 2 x 0.22 x 1.5 mm ² flexible without cable end
	Captive screw clamp terminals, removable terminal block, 2 x 0.252 x 1 mm ² flexible with cable end, with bezel
	Captive screw clamp terminals, removable terminal block, 2 x 0.52 x 1.5 mm 2 flexible with cable end, with double bezel
Current Consumption	8 mA at 28 V DC on power supply
Mounting Support	35 mm symmetrical DIN rail
Net Weight	0.3 kg

Environment

Standards	EN/IEC 60947-5-1 EN 1088/ISO 14119 EN/IEC 60204-1	
Product Certifications	TÜV UL CSA	
Ip Degree Of Protection	IP20 (terminals) conforming to EN/IEC 60529 IP40 (enclosure) conforming to EN/IEC 60529	
Ambient Air Temperature For Operation	-1055 °C	
Ambient Air Temperature For Storage	-2585 °C	

Packing Units

•	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.4 cm
Package 1 Width	10.7 cm
Package 1 Length	12.5 cm
Package 1 Weight	310.0 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	12
Package 2 Height	15.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	4.076 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

②	Mercury Free	
	Rohs Exemption Information	Yes
	Pvc Free	

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information

Dimensions Drawings

Dimensions

