Product data sheet

Specifications



Low voltage transformer, non ventilated dry type, 3 phase, 112.5kVA, 480V primary, 208Y/ 120V secondary, Type 3R

112T3HNV

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 31,018.00 USD

Main

ProductNon-Ventilated TransformerEnclosure Code24EInsulation Temperature428 °F (220 °C)Phase3 phasePrimary Voltage480 V deltaPower Rating112.5 kVASecondary Voltage208Y/120 VFull Capacity Taps6 2.5 % 2+ 4-Temperature Rise150 °CWinding MaterialAluminium		
Insulation Temperature 428 °F (220 °C) Phase 3 phase Primary Voltage 480 V delta Power Rating 112.5 kVA Secondary Voltage 208Y/120 V Full Capacity Taps 6 2.5 % 2+ 4- Temperature Rise 150 °C	Product	Non-Ventilated Transformer
Phase 3 phase Primary Voltage 480 V delta Power Rating 112.5 kVA Secondary Voltage 208Y/120 V Full Capacity Taps 6 2.5 % 2+ 4- Temperature Rise 150 °C	Enclosure Code	24E
Primary Voltage 480 V delta Power Rating 112.5 kVA Secondary Voltage 208Y/120 V Full Capacity Taps 6 2.5 % 2+ 4- Temperature Rise 150 °C	Insulation Temperature	428 °F (220 °C)
Power Rating 112.5 kVA Secondary Voltage 208Y/120 V Full Capacity Taps 6 2.5 % 2+ 4- Temperature Rise 150 °C	Phase	3 phase
Secondary Voltage 208Y/120 V Full Capacity Taps 6 2.5 % 2+ 4- Temperature Rise 150 °C	Primary Voltage	480 V delta
Full Capacity Taps 6 2.5 % 2+ 4- Temperature Rise 150 °C	Power Rating	112.5 kVA
Temperature Rise 150 °C	Secondary Voltage	208Y/120 V
	Full Capacity Taps	6 2.5 % 2+ 4-
Winding Material Aluminium	Temperature Rise	150 °C
	Winding Material	Aluminium

Ordering and shipping details

Category	US10PE216273
Discount Schedule	0PE2
Gtin	785901340270
Returnability	No

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	52.99 in (134.6 cm)
Package 1 Width	29.49 in (74.9 cm)
Package 1 Length	35.98 in (91.4 cm)
Package 1 Weight	1280.00 lb(US) (580.598 kg)

Contractual warranty

Warranty

18 months

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc

Toxic Heavy Metal Free	
Mercury Free	
Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Phenyl Glycidyl Ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov