# **Product datasheet**





# TeSys D contactor - 3P(3 NO) - AC-3 - <= 440 V 65 A - 24 V AC 50/60 Hz coil

Local distributor code: 390826460

LC1D65AB7

EAN Code: 3389119408936

### Main

Range	TeSys TeSys Deca	
Range Of Product	TeSys Deca	
Product Or Component Type	Contactor	
Device Short Name	LC1D	
Contactor Application	Motor control Resistive load	
Utilisation Category	AC-4 AC-1 AC-3 AC-3e	
Poles Description	3P	
[Ue] Rated Operational Voltage	Power circuit: <= 690 V AC 25400 Hz Power circuit: <= 300 V DC	
[le] Rated Operational Current	80 A (at <60 °C) at <= 440 V AC AC-1 for power circuit 65 A (at <60 °C) at <= 440 V AC AC-3 for power circuit 65 A (at <60 °C) at <= 440 V AC AC-3e for power circuit	
[Uc] Control Circuit Voltage	24 V AC 50/60 Hz	

# Complementary

Motor Power Kw	11 kW at 400 V AC 50/60 Hz (AC-4)	
	18.5 kW at 220230 V AC 50/60 Hz (AC-3)	
	30 kW at 380400 V AC 50/60 Hz (AC-3)	
	37 kW at 500 V AC 50/60 Hz (AC-3)	
	37 kW at 660690 V AC 50/60 Hz (AC-3)	
	18.5 kW at 220230 V AC 50/60 Hz (AC-3e)	
	30 kW at 380400 V AC 50/60 Hz (AC-3e)	
	37 kW at 500 V AC 50/60 Hz (AC-3e)	
	37 kW at 660690 V AC 50/60 Hz (AC-3e)	
Motor Power Hp	40 hp at 460/480 V AC 50/60 Hz for 3 phases motors	
	5 hp at 115 V AC 50/60 Hz for 1 phase motors	
	10 hp at 230/240 V AC 50/60 Hz for 1 phase motors	
	20 hp at 200/208 V AC 50/60 Hz for 3 phases motors	
	20 hp at 230/240 V AC 50/60 Hz for 3 phases motors	
	50 hp at 575/600 V AC 50/60 Hz for 3 phases motors	
Compatibility Code	LC1D	
Pole Contact Composition	3 NO	
Protective Cover	With	
[Ith] Conventional Free Air	10 A (at 60 °C) for signalling circuit	
Thermal Current	80 A (at 60 °C) for power circuit	
Irms Rated Making Capacity	140 A AC for signalling circuit conforming to IEC 60947-5-1	
	250 A DC for signalling circuit conforming to IEC 60947-5-1	
	1000 A at 440 V for power circuit conforming to IEC 60947	

Life Is On Schneider 23 Apr 2024

Rated Breaking Capacity	1000 A at 440 V for power circuit conforming to IEC 60947
[Icw] Rated Short-Time Withstand Current	640 A 40 °C - 10 s for power circuit 900 A 40 °C - 1 s for power circuit 110 A 40 °C - 10 min for power circuit 260 A 40 °C - 1 min for power circuit 100 A - 1 s for signalling circuit
	120 A - 500 ms for signalling circuit 140 A - 100 ms for signalling circuit
Associated Fuse Rating	10 A gG for signalling circuit conforming to IEC 60947-5-1 125 A gG at <= 690 V coordination type 1 for power circuit 125 A gG at <= 690 V coordination type 2 for power circuit
Average Impedance	1.5 mOhm - Ith 80 A 50 Hz for power circuit
Power Dissipation Per Pole	9.6 W AC-1 6.3 W AC-3 6.3 W AC-3e
[Ui] Rated Insulation Voltage	Power circuit: 600 V CSA certified Power circuit: 600 V UL certified Signalling circuit: 690 V conforming to IEC 60947-1 Signalling circuit: 600 V CSA certified Signalling circuit: 600 V UL certified Power circuit: 690 V conforming to IEC 60947-4-1
Overvoltage Category	III
Pollution Degree	3
[Uimp] Rated Impulse Withstand Voltage	6 kV conforming to IEC 60947
Safety Reliability Level	B10d = 1369863 cycles contactor with nominal load conforming to EN/ISO 13849-1 B10d = 20000000 cycles contactor with mechanical load conforming to EN/ISO 13849-1
Mechanical Durability	6 Mcycles
Electrical Durability	1.4 Mcycles 80 A AC-1 at Ue <= 440 V 1.45 Mcycles 65 A AC-3 at Ue <= 440 V 1.45 Mcycles 65 A AC-3e at Ue <= 440 V
Control Circuit Type	AC at 50/60 Hz standard
Coil Technology	Without built-in suppressor module
Control Circuit Voltage Limits	0.30.6 Uc (-4070 °C):drop-out AC 50/60 Hz 0.81.1 Uc (-4060 °C):operational AC 50 Hz 0.851.1 Uc (-4060 °C):operational AC 60 Hz 11.1 Uc (6070 °C):operational AC 50/60 Hz
Inrush Power In Va	140 VA 60 Hz cos phi 0.75 (at 20 °C) 160 VA 50 Hz cos phi 0.75 (at 20 °C)
Hold-In Power Consumption In Va	13 VA 60 Hz cos phi 0.3 (at 20 °C) 15 VA 50 Hz cos phi 0.3 (at 20 °C)
Heat Dissipation	45 W at 50/60 Hz
Operating Time	419 ms opening 1226 ms closing
Maximum Operating Rate	3600 cyc/h 60 °C

Connections - Terminals	Control circuit: screw clamp terminals 2 12.5 mm² - cable stiffness: flexible with	
	cable end  Control circuit: screw clamp terminals 1 14 mm² - cable stiffness: flexible without	
	cable end  Control circuit: screw clamp terminals 2 14 mm² - cable stiffness: flexible without	
	cable end Control circuit: screw clamp terminals 1 14 mm² - cable stiffness: flexible with cable	
	end	
	Control circuit: screw clamp terminals 1 14 mm <sup>2</sup> - cable stiffness: solid without cable end	
	Control circuit: screw clamp terminals 2 14 mm² - cable stiffness: solid without cable end	
	Power circuit: screw connection 1 135 mm² - cable stiffness: flexible without cable	
	end Power circuit: screw connection 2 125 mm² - cable stiffness: flexible without cable	
	end Power circuit: screw connection 1 135 mm² - cable stiffness: flexible with cable end	
	Power circuit: screw connection 2 125 mm² - cable stiffness: flexible with cable end	
	Power circuit: screw connection 1 135 mm² - cable stiffness: solid without cable end	
	Power circuit: screw connection 2 125 mm² - cable stiffness: solid without cable end	
Tightening Torque	Control circuit: 1.7 N.m - on EverLink BTR screw connectors - with screwdriver flat $\varnothing$ 6 mm	
	Control circuit: 1.7 N.m - on EverLink BTR screw connectors - with screwdriver Philips No 2	
	Power circuit: 8 N.m - on EverLink BTR screw connectors - cable 2535 mm²	
	hexagonal screw head 4 mm Power circuit: 5 N.m - on EverLink BTR screw connectors - cable 125 mm²	
	hexagonal screw head 4 mm  Control circuit: 1.7 N.m - on EverLink BTR screw connectors - with screwdriver	
	pozidriv No 2	
	Power circuit: 2.5 N.m - on EverLink BTR screw connectors - with screwdriver pozidriv No 2	
Auxiliary Contact Composition	1 NO + 1 NC	
Auxiliary Contacts Type	type mechanically linked 1 NO + 1 NC conforming to IEC 60947-5-1 type mirror contact 1 NC conforming to IEC 60947-4-1	
Signalling Circuit Frequency	25400 Hz	
Minimum Switching Voltage	17 V for signalling circuit	
Minimum Switching Current	5 mA for signalling circuit	
Insulation Resistance	> 10 MOhm for signalling circuit	
Non-Overlap Time	1.5 ms on de-energisation between NC and NO contact 1.5 ms on energisation between NC and NO contact	
Mounting Support	Rail Plate	
Environment		
Standards	CSA C22.2 No 14	
	EN 60947-4-1 EN 60947-5-1	
	IEC 60947-4-1	
	IEC 60947-5-1	
	UL 508 IEC 60335-1	
Product Certifications	UL	
	000	
	CSA GOST	
Ip Degree Of Protection	IP20 front face conforming to IEC 60529	
Protective Treatment	TH conforming to IEC 60068-2-30	
Climatic Withstand	conforming to IACS E10 exposure to damp heat	
	conforming to IEC 60947-1 Annex Q category D exposure to damp heat	

ermissible Ambient Air -4060 °C		
Temperature Around The Device	6070 °C with derating	
Operating Altitude	03000 m	
Fire Resistance	850 °C conforming to IEC 60695-2-1	
Flame Retardance	V1 conforming to UL 94	
Mechanical Robustness	Vibrations contactor open (2 Gn, 5300 Hz)	
	Vibrations contactor closed (4 Gn, 5300 Hz)	
	Shocks contactor closed (15 Gn for 11 ms)	
	Shocks contactor open (10 Gn for 11 ms)	
Height	122 mm	
Width	55 mm	
Depth	120 mm	
Net Weight	0.86 kg	

# **Packing Units**

_	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.0 cm
Package 1 Width	13.5 cm
Package 1 Length	15.2 cm
Package 1 Weight	926.0 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	10
Package 2 Height	15.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	9.945 kg
Unit Type Of Package 3	P06
Number Of Units In Package 3	160
Package 3 Height	77.0 cm
Package 3 Width	80.0 cm
Package 3 Length	60.0 cm
Package 3 Weight	167.62 kg

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance


<b>⊘</b>	Reach Free Of Svhc	
<b>⊘</b>	Toxic Heavy Metal Free	
<b>⊘</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information Yes	
<b>Ø</b>	Pvc Free	

### **Certifications & Standards**

Reach Regulation	REACh Declaration	
Eu Rohs Directive	Compliant EU RoHS Declaration	
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)	
Environmental Disclosure	Product Environmental Profile	
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins	
Circularity Profile	End of Life Information	

## **Dimensions Drawings**

### **Dimensions**



#### (1) Minimum electrical clearance

LC1		D40AD65A
а		55
	with LA4 D●2	_
b1	with LA4 DB3 or LAD 4BB3	136
В	with LA4 DF, DT	157
	with LA4 DM, DW, DL	166
C	without cover or add-on blocks	118
	with cover, without add-on blocks	120
24	with LAD N (1 contact)	_
c1	with LAD N or C (2 or 4 contacts)	150
c2	with LA6 DK10, LAD 6DK	163
23	with LAD T, R, S	171
с3	with LAD T, R, S and sealing cover	175

Connections and Schema

Wiring

