# **Product datasheet**

Specifications





# Capacitor contactor, TeSys D, 63 kVAR at 400 V/50 Hz, coil 230 V AC 50/60 Hz

Local distributor code: 402838443

LC1DWK12P7

EAN Code: 3389110060577

#### Main

Range	TeSys	
Product Name	TeSys LC1D.K	
	TeSys Deca	
Product Or Component Type	Capacitor duty contactor	
Device Short Name	LC1DWK	
Device Application	Control	
Contactor Application	Power factor correction	
Utilisation Category	AC-6b 3P	
Poles Description		
Power Pole Contact Composition	3 NO	
[Ue] Rated Operational Voltage	Power circuit: 690 V AC 50/60 Hz	
Reactive Power Rating	35 kvar at 230 V AC 50 Hz 60 °C	
	63 kvar at 400 V AC 50 Hz 60 °C	
	67 kvar at 440 V AC 50 Hz 60 °C	
	104 kvar at 690 V AC 50 Hz 60 °C	
	30 kvar at 230 V AC 60 Hz 60 °C	
	60 kvar at 460 V AC 60 Hz 60 °C	
	80 kvar at 575 V AC 60 Hz 60 °C	
Control Circuit Type	AC at 50/60 Hz	
[Uc] Control Circuit Voltage	230 V AC 50/60 Hz	
Auxiliary Contact Composition	1 NO + 2 NC instantaneous	
Electrical Durability	300000 cycles at Ue 400 V	
	200000 cycles at Ue 690 V	
Mounting Support	DIN rail	
	Plate	
Standards	EN/IEC 60947-1	
	EN/IEC 60947-4-1	
	UL 60947-4-1	
	CSA C22.2 No 60947-4-1	
Product Certifications	IECEE CB Scheme	
	UL	
	CSA	
	UKCA	

Connections - Terminals	Control circuit: screw clamp terminals 1 14 mm <sup>2</sup> - cable stiffness: solid Control circuit: screw clamp terminals 2 14 mm <sup>2</sup> - cable stiffness: solid Control circuit: screw clamp terminals 1 14 mm <sup>2</sup> - cable stiffness: flexible without cable end Control circuit: screw clamp terminals 2 14 mm <sup>2</sup> - cable stiffness: flexible without
	cable end Control circuit: screw clamp terminals 1 14 mm <sup>2</sup> - cable stiffness: flexible with cable end
	Control circuit: screw clamp terminals 2 12.5 mm <sup>2</sup> - cable stiffness: flexible with cable end
	Power circuit: connector 1 450 mm² - cable stiffness: solid Power circuit: connector 2 425 mm² - cable stiffness: solid
	Power circuit: connector 2 425 mm <sup>2</sup> - cable stiffness: slow Power circuit: connector 2 425 mm <sup>2</sup> - cable stiffness: flexible without cable end Power circuit: connector 2 450 mm <sup>2</sup> - cable stiffness: flexible with cable end Power circuit: connector 2 416 mm <sup>2</sup> - cable stiffness: flexible with cable end
Tightening Torque	Power circuit: 12 N.m - on connector Control circuit: 1.7 N.m - on screw clamp terminals
Maximum Operating Rate	240 cyc/h

### Complementary

Auxiliary Contacts Type type mechanically linked 1 NO + 2 NC conforming to IEC 60947-5-1

### Environment

Ip Degree Of Protection	IP20 front face conforming to IEC 60529
Ambient Air Temperature For Operation	-560 °C
Ambient Air Temperature For Storage	-6080 °C
Operating Altitude	03000 m
Height	180 mm
Width	85 mm
Depth	154 mm
Net Weight	1.65 kg

### **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	13.000 cm
Package 1 Width	17.000 cm
Package 1 Length	18.500 cm
Package 1 Weight	1.790 kg
Unit Type Of Package 2	S04
Number Of Units In Package 2	8
Package 2 Height	30.000 cm
Package 2 Width	40.000 cm
Package 2 Length	60.000 cm
Package 2 Weight	14.970 kg
Unit Type Of Package 3	P06
Number Of Units In Package 3	48
Package 3 Height	75.000 cm

Package 3 Width	80.000 cm
Package 3 Length	60.000 cm
Package 3 Weight	97.820 kg

# **Contractual warranty**

Warranty

18 months

### Sustainability Screen

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Reach Free Of Svhc

Toxic Heavy Metal Free	
Mercury Free	
Rohs Exemption Information	Yes

### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations