

Product data sheet

Specifications



NEMA Motor Starter, Type S,
replacement coil, 220/240VAC
50/60Hz, 2 or 3 pole, NEMA Size 2
starters, 8903SP lighting

3106340947

Product availability: Stock - Normally stocked in distribution facility

Price*: 140.00 USD

Main

Product Or Component Type	Coil
Accessory / Separate Part Destination	Class 8502 type SD contactor Class 8903 type SP lighting contactor

Complementary

Nema Size	2
[Ue] Rated Operational Voltage	240 V AC 60 Hz 220 V AC 50 Hz
Inrush Power In Va	296 VA 311 VA
Average Consumption	36 VA 37 VA
Height	2.61 in (66.2 mm)
Width	3.98 in (101.1 mm)
Depth	2.43 in (61.7 mm)

Ordering and shipping details

Category	US10CP118061
Discount Schedule	0CP1
Gtin	785901504979
Returnability	Yes
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.60 in (6.604 cm)
Package 1 Width	2.50 in (6.35 cm)
Package 1 Length	4.00 in (10.16 cm)
Package 1 Weight	12.96 oz (367.41 g)

Contractual warranty

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Warranty

18 months

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive	Not applicable, out of EU RoHS legal scope
-------------------	--
