Product datasheet

Specifications





TeSys LE - enclosed DOL starter -35 A - 240 V AC coil

Local distributor code: 381827135

LE1D35U7

EAN Code: 3389110589696

Main

| Range | TeSys |
|---------------------------|---|
| Product Name | TeSys LE |
| Device Short Name | LE1D |
| Product Or Component Type | Enclosed DOL starter |
| Device Application | Standard |
| Utilisation Category | AC-3 |
| Device Composition | Thermal overload relay ordered separately Contactor |
| Control Type | Push-button start green I Push-button stop/reset red O |

Complementary

| Motor Power Kw | 15 kW at 380/400 V AC 50/60 Hz 15 kW at 415 V AC 50/60 Hz 15 kW at 440 V AC 50/60 Hz 7.5 kW at 220/230 V AC 50/60 Hz 18.5 kW at 500 V AC 50/60 Hz 18.5 kW at 660/690 V AC 50/60 Hz |
|--|---|
| [Ith] Conventional Free Air Thermal Current | 26.5 A |
| [Uc] Control Circuit Voltage | 240 V AC 50/60 Hz |
| Cable Entry Number | 2 ISO20 top 2 ISO25 top 2 ISO20 bottom 2 ISO25 bottom |
| Width | 101 mm |
| Height | 201 mm |
| Depth | 153.5 mm |
| Net Weight | 4.32 kg |
| | |

Environment

| Material | Polycarbonate |
|--|------------------------------|
| Ip Degree Of Protection | IP65 conforming to IEC 60529 |
| Ik Degree Of Protection | IK07 conforming to IEC 60529 |
| Standards | IEC 60947-4-1 |
| Ambient Air Temperature For Operation | -540 °C |
| Environmental Characteristic | Standard environment |

| Product | Certifications |
|---------|----------------|
|---------|----------------|

UKCA

| Packing Units | | |
|------------------------------|---------|--|
| Unit Type Of Package 1 | PCE | |
| Number Of Units In Package 1 | 1 | |
| Package 1 Height | 19.5 cm | |

| Package 1 Height | 19.5 cm |
|------------------------------|----------|
| Package 1 Width | 16.5 cm |
| Package 1 Length | 25 cm |
| Package 1 Weight | 1.246 kg |
| Unit Type Of Package 2 | \$04 |
| Number Of Units In Package 2 | 5 |
| Package 2 Height | 30 cm |
| Package 2 Width | 40 cm |
| Package 2 Length | 60 cm |
| Package 2 Weight | 6.975 kg |

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

Certifications & Standards

| Reach Regulation | REACh Declaration |
|--------------------------|---|
| Eu Rohs Directive | Compliant EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration |
| Environmental Disclosure | Product Environmental Profile |
| Weee | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |
| Circularity Profile | End of Life Information |