Product datasheet

Specification





TeSys LRD thermal overload relays - 1.6...2.5 A - class 10A

Local distributor code: 402958857

02958857 LRD073

EAN Code: 3389110822038

Main

Range	TeSys	
	TeSys Deca	
Product Name	TeSys LRD	
	TeSys Deca	
Product Or Component Type	Differential thermal overload relay	
Device Short Name	LRD	
Relay Application	Motor protection	
Product Compatibility	LC1D09	
	LC1D32	
	LC1D25	
	LC1D38	
	LC1D12	
	LC1D18	
Network Type	DC	
	AC	
Thermal Overload Class	Class 10A conforming to IEC 60947-4-1	
Thermal Protection Adjustment Range	1.62.5 A	
[Ui] Rated Insulation Voltage	Power circuit: 600 V conforming to CSA	
	Power circuit: 600 V conforming to UL	
	Power circuit: 690 V conforming to IEC 60947-4-1	

Complementary

Network Frequency	0400 Hz
Mounting Support	Plate, with specific accessories
	Rail, with specific accessories
	Under contactor
Tripping Threshold	1.14 +/- 0.06 Ir conforming to IEC 60947-4-1
Auxiliary Contact Composition	1 NO + 1 NC
[Ith] Conventional Free Air Thermal Current	5 A for signalling circuit
Permissible Current	3 A at 120 V AC-15 for signalling circuit
	0.22 A at 125 V DC-13 for signalling circuit
[Ue] Rated Operational Voltage	690 V AC 0400 Hz for power circuit conforming to IEC 60947-4-1
Associated Fuse Rating	4 A gG for signalling circuit
•	4 A BS for signalling circuit
[Uimp] Rated Impulse Withstand Voltage	6 kV
Phase Failure Sensitivity	Tripping current 130 % of Ir on two phase, the last one at 0
Control Type	Red push-button: stop
	Blue push-button: reset

Temperature Compensation	-2060 °C	
Connections - Terminals	Control circuit: spring terminals 1 cable(s) 12.5 mm² solid without cable end Control circuit: spring terminals 1 cable(s) 12.5 mm² flexible without cable end Power circuit: spring terminals 1 cable(s) 1.54 mm² flexible without cable end Power circuit: spring terminals 1 cable(s) 1.54 mm² flexible with cable end	
Height	93 mm	
Width	45 mm	
Depth	72 mm	
Net Weight	0.14 kg	

Environment

Climatic Withstand	conforming to IACS E10	
Ip Degree Of Protection	IP20 conforming to IEC 60529	
Ambient Air Temperature For Operation	-2060 °C without derating conforming to IEC 60947-4-1	
Ambient Air Temperature For Storage	-6070 °C	
Flame Retardance	V1 conforming to UL 94	
Mechanical Robustness	Vibrations: 6 Gn conforming to IEC 60068-2-6 Shocks: 15 Gn for 11 ms conforming to IEC 60068-2-7	
Dielectric Strength	1.89 kV at 50 Hz conforming to IEC 60947-1	
Standards	EN/IEC 60947-4-1 EN/IEC 60947-5-1 UL 60947-4-1 UL 60947-5-1 CSA C22.2 No 60947-4-1 CSA C22.2 No 60947-5-1 GB/T 14048.4 GB/T 14048.5 EN 50495	
Product Certifications	IEC UL CSA CCC EAC BV RINA DNV-GL LROS (Lloyds register of shipping) ATEX INERIS UKCA	

Packing Units

•	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.5 cm
Package 1 Width	7.8 cm
Package 1 Length	10 cm
Package 1 Weight	191 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	23
Package 2 Height	15 cm
Package 2 Width	30 cm
Package 2 Length	40 cm

Package 2 Weight

4.698 kg

Contractual warranty

Warranty

18 months

Sustainability Green Premium

Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Reach Free Of Svhc



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information