

Product data sheet

Specifications



Multi9 - C60 UL489 - MCB - 3P - 8 A - D Curve - 240 V - 10 kA - fingersafe

60292F

⚠ Discontinued on: Jan 23, 2021

⚠ Discontinued

Main

Range	Multi9
Product Or Component Type	Miniature circuit-breaker
Product Name	Multi9 C60
Device Short Name	C60 UL489
Device Application	Distribution
Number Of Protected Poles	3
Line Rated Current	8 A 77 °F (25 °C)
Network Type	AC
Trip Unit Technology	Thermal-magnetic
Suitability For Isolation	Yes EN/IEC 60947-2

Complementary

System Voltage	240 V 415 V 440 V
Mounting Mode	Clip-on
Poles Description	3P
Interrupt Rating	10 kA 10 kA 20 kA 10 kA 6 kA 20 kA 10 kA 6 kA
Network Frequency	50/60 Hz
Curve Code	D
Magnetic Tripping Limit	12 x In +/- 20 % AC
Limitation Class	3 EN/IEC 60947-2
[UI] Rated Insulation Voltage	500 V AC EN/IEC 60947-2
[Uimp] Rated Impulse Withstand Voltage	6 kVEN/IEC 60947-2
Contact Position Indicator	Yes
Control Type	Toggle
Local Signalling	ON/OFF indication

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Mounting Support	DIN rail
9 Mm Pitches	6
Height	4.84 in (123 mm)
Width	2.13 in (54 mm)
Depth	2.87 in (73 mm)
Net Weight	0.73 lb(US) (0.33 kg)
Color	Gray
Mechanical Durability	20000 cycles
Electrical Durability	10000 cycles
Provision For Padlocking	Padlockable
Connections - Terminals	Ring terminal top or bottom)
Tightening Torque	17.70 lbf.in (2 N.m) top or bottom

Environment

Standards	UL 489 CSA C22.2 No 5 GB 14048.2 EN/IEC 60947-2
Product Certifications	CSA CCC IEC UL
Ip Degree Of Protection	IP40 (modular enclosure) conforming to IEC 60529 IP10 conforming to IEC 60529
Pollution Degree	3 EN/IEC 60947-2
Overvoltage Category	IV
Tropicalisation	2 IEC 60068-1
Relative Humidity	95 % 131 °F (55 °C)
Operating Altitude	6561.68 ft (2000 m)
Ambient Air Temperature For Operation	-22...158 °F (-30...70 °C)
Ambient Air Temperature For Storage	-40...176 °F (-40...80 °C)

Ordering and shipping details

Category	00915-C60N MINIATURE CIRCUIT BREAKER-UL489
Discount Schedule	DE2
Returnability	No
Country Of Origin	FR

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	13.60 oz (385.554 g)

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

- [Learn more about Green Premium >](#)
- [Guide to assess a product’s sustainability >](#)



RoHS/REACH

Well-being performance

✓ Mercury Free	
✓ Rohs Exemption Information	Yes
✓ Halogen Free Product	

Certifications & Standards

Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Weeee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.