# **Product datasheet**

Specification





# TeSys LRD thermal overload relays - 17...25 A - class 10A

Local distributor code:

392688321 LRD325

EAN Code: 3389119215473

#### Main

Range	TeSys TeSys Deca	
Product Name	TeSys LRD TeSys Deca	
Product Or Component Type	Differential thermal overload relay	
Device Short Name	LRD	
Relay Application	Motor protection	
Product Compatibility	LC1D40A LC1D65A LC1D50A	
Network Type	DC AC	
Thermal Overload Class	Class 10A conforming to IEC 60947-4-1	
Thermal Protection Adjustment Range	rotection Adjustment 1725 A	
[Ui] Rated Insulation Voltage	Power circuit: 600 V conforming to CSA Power circuit: 600 V conforming to UL Power circuit: 690 V conforming to IEC 60947-4-1	

## Complementary

-		
Network Frequency	0400 Hz	
Mounting Support	Plate, with specific accessories Rail, with specific accessories Under contactor	
Tripping Threshold	1.14 +/- 0.06 Ir conforming to IEC 60947-4-1	
Auxiliary Contact Composition	1 NO + 1 NC	
[Ith] Conventional Free Air Thermal Current	5 A for signalling circuit	
Permissible Current	0.95 A at 380 V AC-15 for signalling circuit 0.06 A at 440 V DC-13 for signalling circuit	
[Ue] Rated Operational Voltage	690 V AC 0400 Hz for power circuit conforming to IEC 60947-4-1	
Associated Fuse Rating	4 A gG for signalling circuit 4 A BS for signalling circuit	
[Uimp] Rated Impulse Withstand Voltage	d 6 kV	
Phase Failure Sensitivity	Tripping current 130 % of Ir on two phase, the last one at 0	
Control Type	Red push-button: stop Blue push-button: reset	
Temperature Compensation	-2060 °C	

Connections - Terminals	Control circuit: screw clamp terminals 2 cable(s) 12.5 mm² flexible without cable end Control circuit: screw clamp terminals 2 cable(s) 12.5 mm² flexible with cable end Control circuit: screw clamp terminals 2 cable(s) 12.5 mm² flexible with cable end Power circuit: EverLink BTR screw connectors 1 cable(s) 135 mm² flexible without cable end Power circuit: EverLink BTR screw connectors 1 cable(s) 135 mm² flexible with cable end Power circuit: EverLink BTR screw connectors 1 cable(s) 135 mm² solid without cable end
Tightening Torque	Control circuit: 1.7 N.m - on screw clamp terminals Power circuit: 5 N.m - on EverLink BTR screw connectors
Height	70 mm
Width	55 mm
Depth	123 mm
Net Weight	0.375 kg

## **Environment**

Climatic Withstand	conforming to IACS E10	
Ip Degree Of Protection	IP20 conforming to IEC 60529	
Ambient Air Temperature For Operation	Temperature For -2060 °C without derating conforming to IEC 60947-4-1	
Ambient Air Temperature For Storage	-6070 °C	
Flame Retardance	V1 conforming to UL 94	
Mechanical Robustness	Shocks: 15 Gn for 11 ms conforming to IEC 60068-2-7 Vibrations: 4 gn conforming to IEC 60068-2-6	
Dielectric Strength	1.89 kV at 50 Hz conforming to IEC 60947-1	
Standards	EN/IEC 60947-4-1 EN/IEC 60947-5-1 UL 60947-4-1 UL 60947-5-1 CSA C22.2 No 60947-4-1 CSA C22.2 No 60947-5-1 GB/T 14048.4 GB/T 14048.5 EN 50495	
Product Certifications	IEC UL CSA CCC EAC DNV-GL RMRS EU-RO MR LROS (Lloyds register of shipping) ATEX INERIS UKCA	

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.000 cm
Package 1 Width	11.000 cm
Package 1 Length	14.000 cm
Package 1 Weight	390.000 g
Unit Type Of Package 2	S02

Number Of Units In Package 2	13
Package 2 Height	15.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	5.424 kg
Unit Type Of Package 3	P06
Number Of Units In Package 3	208
Package 3 Height	75.000 cm
Package 3 Width	60.000 cm
Package 3 Length	80.000 cm
Package 3 Weight	96.900 kg

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance

<b>⊘</b>	Reach Free Of Svhc	
<b>9</b>	Toxic Heavy Metal Free	
<b>⊘</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information