

# Product datasheet

Specifications



## TeSys LT47 electronic over current relays - automatic - 0.5...6 A - 24 V AC/DC

LT4706BA

⚠ Discontinued on: 30 Jun 2023

⚠ Discontinued

EAN Code: 8809755436414

### Main

Range	TeSys
Product Name	TeSys LT
Product Or Component Type	Electronic over current relay
Device Short Name	LT47
Device Application	Protection
Relay Application	Locked rotor, mechanical jamming $I > 3 \times I_{setting}$ Overload $I_{max} > I_{setting}$ Sensitivity to phase failure
[Us] Rated Supply Voltage	24 V AC 24 V DC
Thermal Protection Adjustment Range	0.5...6 A
[Ui] Rated Insulation Voltage	Power circuit: 600 V AC conforming to CSA Power circuit: 600 V AC conforming to UL Power circuit: 690 V AC conforming to IEC 60947-4-1

### Complementary

Network Frequency	50...60 Hz
Mounting Support	Rail
Tripping Threshold	0.5...5 A
Electromagnetic Compatibility	Resistance to electrostatic discharge: 8 kV in open air conforming to IEC 61000-4-2 Resistance to electrostatic discharge: 6 kV in direct mode conforming to IEC 61000-4-2 Conducted emission: class A conforming to EN 55011 Immunity to electromagnetic interference: 10 V/m conforming to IEC 61000-4-3 Immunity to fast transients: 2 kV conforming to IEC 61000-4-4 Surge withstand: 6 kV conforming to IEC 61000-4-5 Conducted HF disturbances: 10 V conforming to IEC 61000-4-6
Auxiliary Contact Composition	1 NO + 1 NC
[Ith] Conventional Free Air Thermal Current	3 A for signalling circuit
Associated Fuse Rating	3 A gG for signalling circuit 3 A BS for signalling circuit
[Uimp] Rated Impulse Withstand Voltage	6 kV
Time Range	1...120 s - control type R-time 0.3...30 s - control type O-time
Local Signalling	1 LED (green) 1 LED (red)
Control Type	automatic: reset

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Connections - Terminals	Signalling circuit: screw clamp terminals 1 1...2.5 mm² - cable stiffness: flexible with cable end Signalling circuit: screw clamp terminals 1 1...2.5 mm² - cable stiffness: flexible without cable end Signalling circuit: screw clamp terminals 2 1...2.5 mm² - cable stiffness: flexible with cable end Signalling circuit: screw clamp terminals 2 1...2.5 mm² - cable stiffness: flexible without cable end Signalling circuit: lugs-ring terminals - external diameter: 7 mm
Tightening Torque	Signalling circuit: 1.7 N.m M3.5
Height	70.3 mm
Width	71 mm
Depth	77.2 mm
Net Weight	0.192 kg

## Environment

Standards	IEC 60255-6 IEC 60947
Product Certifications	UL CSA
Protective Treatment	TH conforming to IEC 60068
Ip Degree Of Protection	IP20 conforming to IEC 60529 IP20 conforming to VDE 0106
Ambient Air Temperature For Operation	-25...60 °C without derating conforming to IEC 60947-4-1
Ambient Air Temperature For Storage	-30...80 °C
Operating Altitude	2000 m
Mechanical Robustness	Shocks: 15 Gn for 11 ms conforming to IEC 60068-2-7 Vibrations: 4 gn conforming to IEC 60068-2-6
Dielectric Strength	2 kV at 50 Hz conforming to IEC 60255-5

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.6 cm
Package 1 Width	8.3 cm
Package 1 Length	7.6 cm
Package 1 Weight	193.0 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	16
Package 2 Height	15.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	3.543 kg
Unit Type Of Package 3	P06
Number Of Units In Package 3	256
Package 3 Height	75 cm
Package 3 Width	40 cm

Package 3 Length	80 cm
Package 3 Weight	74.408 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability



**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Well-being performance

 Mercury Free	
 Rohs Exemption Information	<a href="#">Yes</a>
Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	<a href="#">End of Life Information</a>