Product datasheet

Specifications





Standard control unit, TeSys U, 8-32A, 3P motors, thermal magnetic protection, class 10, coil 48-72V AC/DC

Local distributor code: 389810571

LUCA32ES

(!) Discontinued on: 9 Feb 2023

EAN Code: 3389110363999

Main

IVIAIII		
Range	TeSys	
Range Of Product	TeSys Ultra	
Product Name	TeSys Ultra	
Device Short Name	LUCA	
Product Or Component Type	Standard control unit	
Device Application	Motor control Motor protection	
Product Specific Application	Basic protection requirements for motor starters: overload and short-circuit	
Main Function Available	Earth fault protection Protection against phase failure and phase imbalance Manual reset Protection against overload and short-circuit	
Product Compatibility	Power base LUB32 Power base LUB38 Power base LUB320 Power base LUB380 Reversing contactor breaker LU2B32ES	
[Ue] Rated Operational Voltage	690 V AC	
Network Frequency	4060 Hz	
Load Type	3-phase motor - cooling: self-cooled	
Utilisation Category	AC-41 AC-43 AC-44	
Motor Power Kw	15 kW at 400440 V AC 50/60 Hz 15 kW at 500 V AC 50/60 Hz 18.5 kW at 690 V AC 50/60 Hz	
Rated Motor Current Adjustment Range	832 A	
Thermal Overload Class	Class 10 - frequency limit: 4060 Hz - temperature compensation: -2570 °C conforming to IEC 60947-6-2 Class 10 - frequency limit: 4060 Hz - temperature compensation: -2570 °C conforming to UL 508	
Tripping Threshold	14.2 x Ir +/- 20 %	
Phase Failure Sensitivity	Yes	
[Uc] Control Circuit Voltage	48 V AC 4872 V DC	

Complementary

Life Is On Schneider

Control Circuit Voltage Limits	38.572 V for AC circuit 48 V in operation
	38.593 V for DC circuit 4872 V in operation
	29 V for AC circuit 48 V drop-out 29 V for DC circuit 4872 V drop-out
Typical Current Consumption	280 mA at 48 V AC I maximum while closing with LUB32
	280 mA at 48 V AC I maximum while closing with LUB38
	280 mA at 4872 V DC I maximum while closing with LUB32 280 mA at 4872 V DC I maximum while closing with LUB38
	45 mA at 48 V AC I rms sealed with LUB32
	45 mA at 48 V AC I rms sealed with LUB38
	45 mA at 4872 V DC I rms sealed with LUB32
	45 mA at 4872 V DC I rms sealed with LUB38
Heat Dissipation	3 W for control circuit with LUB32
	3 W for control circuit with LUB38
Operating Time	35 ms opening with LUB32 for control circuit
	35 ms opening with LUB38 for control circuit
	60 ms closing with LUB32 for control circuit
	60 ms closing with LUB38 for control circuit
Standards	EN 60947-6-2
	IEC 60947-6-2
	UL 60947-4-1, with phase barrier
	CSA C22.2 No 60947-4-1, with phase barrier
Product Certifications	CE
	UL
	CSA
	CCC
	EAC
	ASEFA ATEX
	Marine
[Ui] Rated Insulation Voltage	690 V conforming to IEC 60947-6-2
	600 V conforming to UL 60947-4-1
	600 V conforming to CSA C22.2 No 60947-4-1
[Uimp] Rated Impulse Withstand Voltage	6 kV conforming to IEC 60947-6-2
Safe Separation Of Circuit	400 V SELV between the control and auxiliary circuits conforming to IEC 60947-1
	400 V SELV between the control or auxiliary circuit and the main circuit conforming to
	IEC 60947-1
Fixing Mode	Plug-in (front face)
Width	45 mm
Height	66 mm
	00 mm
Depth	60 mm
Net Weight	0.135 kg
Compatibility Code	LUCA
Environment	
Ip Degree Of Protection	IP20 front panel and wired terminals conforming to IEC 60947-1
	IP20 other faces conforming to IEC 60947-1
	IP40 front panel outside connection zone conforming to IEC 60947-1
Protective Treatment	TH conforming to IEC 60068
Ambient Air Temperature For	-2570 °C
Operation	

Operation	-2310 0
Ambient Air Temperature For Storage	-4085 °C
Operating Altitude	2000 m
Fire Resistance	960 °C parts supporting live components conforming to IEC 60695-2-12 650 °C conforming to IEC 60695-2-12
Shock Resistance	10 gn power poles open conforming to IEC 60068-2-27 15 gn power poles closed conforming to IEC 60068-2-27

Vibration Resistance	2 gn, 5300 Hz, power poles open conforming to IEC 60068-2-6	
	4 gn, 5300 Hz, power poles closed conforming to IEC 60068-2-6	
Resistance To Electrostatic	8 kV level 3 in open air conforming to IEC 61000-4-2	
Discharge	8 kV level 4 on contact conforming to IEC 61000-4-2	
Non-Dissipating Shock Wave	1 kV serial mode conforming to IEC 60947-6-2	
	2 kV common mode conforming to IEC 60947-6-2	
Resistance To Radiated Fields	10 V/m 3 conforming to IEC 61000-4-3	
Resistance To Fast Transients	2 kV class 3 serial link conforming to IEC 61000-4-4	
	4 kV class 4 all circuits except for serial link conforming to IEC 61000-4-4	
Immunity To Radioelectric Fields	unity To Radioelectric Fields 10 V conforming to IEC 61000-4-6	
munity To Microbreaks 3 ms		
Immunity To Voltage Dips 70 % / 500 ms conforming to IEC 61000-4-11		

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.000 cm
Package 1 Width	8.000 cm
Package 1 Length	8.500 cm
Package 1 Weight	126.000 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	23
Package 2 Height	15.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	3.194 kg

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free	
Rohs Exemption Information	Yes
Pvc Free	

Halogen Free Plastic Parts Product

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information