# **Product datasheet**

Specifications





## Advanced control unit, TeSys U, 4.5-18A, 3P motors, protection & diagnostic, class 10, coil 48-72V AC/DC

Local distributor code: 389810652

LUCB18ES

(!) Discontinued on: 9 Feb 2023

EAN Code: 3389110364224

#### Main

Man		
Range	TeSys	
Range Of Product	TeSys Ultra	
Product Name	TeSys Ultra	
Device Short Name	LUCB	
Product Or Component Type	Advanced control unit	
Device Application	Motor control Motor protection	
Product Specific Application	Basic protection and advanced functions, communication	
Main Function Available	Protection against overload and short-circuit Protection against phase failure and phase imbalance Manual reset Earth fault protection	
Product Compatibility	Power base LUB32 Power base LUB38 Power base LUB320 Power base LUB380 Reversing contactor breaker LU2B32ES	
[Ue] Rated Operational Voltage	690 V AC	
Network Frequency	4060 Hz	
Load Type	3-phase motor - cooling: self-cooled	
Utilisation Category	AC-44 AC-43 AC-41	
Motor Power Kw	7.5 kW at 400440 V AC 50/60 Hz 9 kW at 500 V AC 50/60 Hz 15 kW at 690 V AC 50/60 Hz	
Rated Motor Current Adjustment Range	4.518 A	
Thermal Overload Class	Class 10 - frequency limit: 4060 Hz - temperature compensation: -2570 °C conforming to IEC 60947-6-2 Class 10 - frequency limit: 4060 Hz - temperature compensation: -2570 °C conforming to UL 508	
Tripping Threshold	14.2 x lr +/- 20 %	
Phase Failure Sensitivity	Yes	
[Uc] Control Circuit Voltage	48 V AC 4872 V DC	

### Complementary

Life Is On Schneider

Control Circuit Voltage Limits	38.572 V for AC circuit 48 V in operation
	38.593 V for DC circuit 4872 V in operation
	29 V for AC circuit 48 V drop-out
	29 V for DC circuit 4872 V drop-out
Typical Current Consumption	280 mA at 48 V AC I maximum while closing with LUB32
	280 mA at 48 V AC I maximum while closing with LUB38
	280 mA at 4872 V DC I maximum while closing with LUB32
	280 mA at 4872 V DC I maximum while closing with LUB38
	45 mA at 48 V AC I rms sealed with LUB32
	45 mA at 48 V AC I rms sealed with LUB38
	45 mA at 4872 V DC I rms sealed with LUB32
	45 mA at 4872 V DC I rms sealed with LUB38
Heat Dissipation	3 W for control circuit with LUB32
	3 W for control circuit with LUB38
Operating Time	35 ms opening with LUB32 for control circuit
	35 ms opening with LUB38 for control circuit
	60 ms closing with LUB32 for control circuit
	60 ms closing with LUB38 for control circuit
Reset	Manual reset
Standards	EN 60947-6-2
	IEC 60947-6-2
	UL 60947-4-1, with phase barrier
	CSA C22.2 No 60947-4-1, with phase barrier
Product Certifications	CE
	UL
	CSA
	CCC
	EAC
	ASEFA
	ATEX
	Marine
[Ui] Rated Insulation Voltage	690 V conforming to IEC 60947-6-2
	600 V conforming to UL 60947-4-1
	600 V conforming to CSA C22.2 No 60947-4-1
[Uimp] Rated Impulse Withstand Voltage	6 kV conforming to IEC 60947-6-2
Safe Separation Of Circuit	400 V SELV between the control and auxiliary circuits conforming to IEC 60947-1
-	400 V SELV between the control or auxiliary circuit and the main circuit conforming to
	IEC 60947-1
Fixing Mode	Plug-in (front face)
Width	45 mm
Height	66 mm
Depth	60 mm
Compatibility Code	LUCB
Environment	

Ip Degree Of Protection	IP20 front panel and wired terminals conforming to IEC 60947-1 IP20 other faces conforming to IEC 60947-1 IP40 front panel outside connection zone conforming to IEC 60947-1
Protective Treatment	TH conforming to IEC 60068
Ambient Air Temperature For Operation	-2570 °C
Ambient Air Temperature For Storage	-4085 °C
Operating Altitude	2000 m
Fire Resistance	960 °C parts supporting live components conforming to IEC 60695-2-12 650 °C conforming to IEC 60695-2-12
Shock Resistance	10 gn power poles open conforming to IEC 60068-2-27 15 gn power poles closed conforming to IEC 60068-2-27

Vibration Resistance	2 gn, 5300 Hz, power poles open conforming to IEC 60068-2-6	
	4 gn, 5300 Hz, power poles closed conforming to IEC 60068-2-6	
Resistance To Electrostatic	8 kV level 3 in open air conforming to IEC 61000-4-2	
Discharge	8 kV level 4 on contact conforming to IEC 61000-4-2	
Non-Dissipating Shock Wave	1 kV serial mode conforming to IEC 60947-6-2	
	2 kV common mode conforming to IEC 60947-6-2	
Resistance To Radiated Fields	10 V/m 3 conforming to IEC 61000-4-3	
Resistance To Fast Transients	2 kV class 3 serial link conforming to IEC 61000-4-4	
	4 kV class 4 all circuits except for serial link conforming to IEC 61000-4-4	
Immunity To Radioelectric Fields	10 V conforming to IEC 61000-4-6	
Immunity To Microbreaks	3 ms	
Immunity To Voltage Dips	b Voltage Dips 70 % / 500 ms conforming to IEC 61000-4-11	

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.5 cm
Package 1 Width	8.5 cm
Package 1 Length	10.2 cm
Package 1 Weight	140.0 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	23
Package 2 Height	15.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	3.425 kg

# **Contractual warranty**

Warranty

18 months

## Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Mercury Free
Rohs Exemption Information Yes
Pvc Free

Halogen Free Plastic Parts Product

### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information