


Specifications



LZ8H2X4BD

EAN Code: 3606485421094

Range	TeSys
Product Name	TeSys Hybrid
Device Short Name	LZ8H
Product Or Component Type	Reversing ultra-compact starter
Motor Starter Type	Direct on line
Poles Description	3P
[Ue] Rated Operational Voltage	500 V AC
[Ie] Rated Operational Current	2.4 A at 500 V AC-51 2.4 A at 500 V AC-53A 2.4 A at 500 V AC-51 mounting side by side 2.4 A at 500 V AC-53A mounting side by side
Thermal Protection Adjustment Range	0.18...2.4 A
Motor Power Kw	0.37 kW at 220 V AC 0.65 0.37 kW at 230 V AC 0.65 0.75 kW at 380 V AC 0.65 0.75 kW at 400 V AC 0.65 0.75 kW at 415 V AC 0.65 0.75 kW at 440 V AC 0.65 1.1 kW at 500 V AC 0.65
Motor Power Hp	0.5 hp at 200 V AC 0.5 hp at 230 V AC 1 hp at 460 V AC
[Uc] Control Circuit Voltage	24 V DC
Safety Level	SIL 3 conforming to IEC 61508-1 stop function PL = e conforming to ISO 13849-1 stop function SIL 2 conforming to IEC 61508-1 motor protection
Safety Reliability Data	MTTFd = 517 years stop function PFHd = 2.67E-9 1/h stop function SFF = 99 % stop function SFF = 99 % motor protection MTTFd = 447 years motor protection
Thermal Overload Class	Class 10A conforming to IEC 60947-4-2

Auxiliary Contact Composition	1 C/O fault signalling
Control Circuit Voltage Limits	19.2...30 V DC
Current Consumption	<= 40 mA at 24 V DC
Reset	Manual Electrical reset
Electrical Durability	30 Mcycles

Maximum Operating Rate	120 cyc/mn AC-51 50 % ON 6 cyc/mn AC-53A 50 % ON
Mounting Mode	By clips
Mounting Support	DIN rail
Connections - Terminals	Screw clamp terminals 1 cable(s) 0.2...2.5 mm² - rigid Screw clamp terminals 1 cable(s) 0.25...2.5 mm² - flexible - with cable end Screw clamp terminals 1 cable(s) 0.2...2.5 mm² - flexible - without cable end
Tightening Torque	0.5...0.6 N.m flat Ø 2.5 mm screwdriver 3 mm
Certifications	CE ATEX as associated device for motor protection in zones 1 and 21 CULus
Standards	IEC 60947-4-2 UL 60947-4-1
[UI] Rated Insulation Voltage	500 V AC 50/60 Hz
[Uimp] Rated Impulse Withstand Voltage	6 kV
Pollution Degree	2
Width	22.5 mm
Height	99 mm
Depth	114.5 mm
Net Weight	212 g

Environment

Ip Degree Of Protection	IP20
Protective Treatment	TC
Ambient Air Temperature For Operation	-25...70 °C without derating
Ambient Air Temperature For Storage	-40...80 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.6 cm
Package 1 Width	12.0 cm
Package 1 Length	12.0 cm
Package 1 Weight	266.0 g
Unit Type Of Package 2	S01
Number Of Units In Package 2	10
Package 2 Height	15.0 cm
Package 2 Width	15.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	2.84 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration	
Eu Rohs Directive	Compliant	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration	
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins	