

Product datasheet

Specifications



Reversing Starter TeSys H Safe-Torque-Off 3kW-400V control 24VDC Spring

Local distributor code:
403007558LZ8H6X53BD

EAN Code: 3606485421261

Main

Range	TeSys
Product Name	TeSys Hybrid
Device Short Name	LZ8H
Product Or Component Type	Reversing ultra-compact starter
Motor Starter Type	Direct on line
Poles Description	3P
[Ue] Rated Operational Voltage	500 V AC
[Ie] Rated Operational Current	6.5 A at 500 V AC-53A 9 A at 500 V AC-51 5 A at 500 V AC-53A mounting side by side 7 A at 500 V AC-51 mounting side by side
Thermal Protection Adjustment Range	1.5...9 A
Motor Power Kw	1.5 kW at 220 V AC 0.65 1.5 kW at 230 V AC 0.65 2.2 kW at 380 V AC 0.65 3 kW at 400 V AC 0.65 3 kW at 415 V AC 0.65 3 kW at 440 V AC 0.65 3 kW at 500 V AC 0.65
Motor Power Hp	1 hp at 200 V AC 1.5 hp at 230 V AC 3 hp at 460 V AC
[Uc] Control Circuit Voltage	24 V DC
Safety Level	SIL 3 conforming to IEC 61508-1 stop function PL = e conforming to ISO 13849-1 stop function SIL 2 conforming to IEC 61508-1 motor protection
Safety Reliability Data	MTTFd = 517 years stop function PFHd = 2.67E-9 1/h stop function SFF = 99 % stop function SFF = 99 % motor protection MTTFd = 447 years motor protection
Thermal Overload Class	Class 10A conforming to IEC 60947-4-2

Complementary

Auxiliary Contact Composition	1 C/O fault signalling
Control Circuit Voltage Limits	19.2...30 V DC
Current Consumption	<= 40 mA at 24 V DC
Reset	Manual Electrical reset
Electrical Durability	30 Mcycles

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Maximum Operating Rate	120 cyc/mn AC-51 50 % ON 6 cyc/mn AC-53A 50 % ON
Mounting Mode	By clips
Mounting Support	DIN rail
Connections - Terminals	Spring clamp terminals 1 cable(s) 0.2...2.5 mm² - rigid Spring clamp terminals 1 cable(s) 0.25...2.5 mm² - flexible - with cable end Spring clamp terminals 1 cable(s) 0.2...2.5 mm² - flexible - without cable end
Certifications	CULus ATEX as associated device for motor protection in zones 1 and 21 CE
Standards	UL 60947-4-1 IEC 60947-4-2
[Ui] Rated Insulation Voltage	500 V AC 50/60 Hz
[Uimp] Rated Impulse Withstand Voltage	6 kV
Pollution Degree	2
Width	22.5 mm
Height	99 mm
Depth	114.5 mm
Net Weight	212 g

Environment

Ip Degree Of Protection	IP20
Protective Treatment	TC
Ambient Air Temperature For Operation	-25...30 °C without derating 30...70 °C with derating
Ambient Air Temperature For Storage	-40...80 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.600 cm
Package 1 Width	11.600 cm
Package 1 Length	12.000 cm
Package 1 Weight	255.000 g
Unit Type Of Package 2	S01
Number Of Units In Package 2	10
Package 2 Height	15.000 cm
Package 2 Width	15.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	2.750 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability





Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	Yes
Reach Regulation		REACH Declaration
Eu Rohs Directive		Compliant EU RoHS Declaration
China Rohs Regulation		China RoHS declaration
Weee		The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins