Product datasheet

Specification





SCREW TERMINAL, 3 LEVELS, 6 POINTS, 2,5MM², GREY

Local distributor code: 397144543

NSYTRV26T

EAN Code: 3606480531880

Main

Range	Linergy	
Product Name	Linergy TR	
Product Or Component Type	Terminal block	
Device Short Name	TRV	
Accessory / Separate Part Category	Connection accessory	
Terminal Block Type	Passthrough	
Terminal Block Level	3	
Mounting Mode	Clip-on	
Nominal Cross Section	2.5 mm²	
Length	90 mm	
Colour	Grey	
Quantity Per Set	Set of 50	

Complementary

Joinplomontal y	
Width	5.2 mm
Height	77.5 mm
Connections - Terminals	1 x screw terminal: upstream (M3) 1 x screw terminal: downstream (M3)
Number Of Connections	2
Connection Position	Sideways
Number Of Measurement Input	3
Cable Cross Section	0.144 mm², solid cable with cable end 0.22.5 mm², flexible cable with cable end 0.144 mm², solid cable without cable end 0.144 mm², flexible cable without cable end
Tightening Torque	0.50.6 N.m
Wire Stripping Length	9 mm
Tool Type	Connection: screwdriver Disconnection: screwdriver
[Ue] Rated Operational Voltage	500 V conforming to EN/IEC 60947-7-1
In] Rated Current 20 A conforming to EN/IEC 60947-7-1	
Material	Polyamide 6/6: insulating case Copper alloy: connector and screw Copper alloy: commoning link Chromium-nickel steel: spring

Dielectric Loss	0.01 at 1 MHz conforming to IEC 60250	
	0.01 at 1 MHz conforming to VDE 0303-T4	
Dielectric Constant	3.7 at 1 MHz	
Resistivity	10000 M Ω .m conforming to IEC 60093 10000 M Ω .m conforming to VDE 0303-T30	
Surface Resistance	ance $1000 \; \text{G}\Omega \; \text{conforming to IEC } 60093$ $1000 \; \text{G}\Omega \; \text{conforming to VDE } 0303\text{-T30}$	
Creep Resistance	500 CTI (> 400 kB) conforming to IEC 60093 500 CTI (> 400 kB) conforming to VDE 0303-T30	
Flame Retardance	V0, thickness0.8 mm conforming to UL 94	
Net Weight	25.1 g	
Range Compatibility	Prisma G Prisma P Prisma PH Prisma Pack Spacial Kaedra Pragma TeSys	
Product Compatibility	Spacial enclosures	

Environment

Product Certifications	EAC CSA cURus	
Dielectric Strength	1000 V conforming to IEC 60243-1	
Ambient Air Temperature For Operation	-40130 °C conforming to IEC 60216-1	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9.500 cm
Package 1 Width	11.000 cm
Package 1 Length	36.500 cm
Package 1 Weight	26.000 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	50
Package 2 Height	9.500 cm
Package 2 Width	11.000 cm
Package 2 Length	36.500 cm
Package 2 Weight	1.324 kg
Unit Type Of Package 3	S03
Number Of Units In Package 3	300
Package 3 Height	30.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	8.456 kg

Contractual warranty

Warranty

18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

②	Mercury Free	
⊘	Rohs Exemption Information	Yes
⊘	Halogen Free Plastic Parts Product	

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations