

Product datasheet

Specifications



on-delay timing relay - 40..3600 s - 240 V AC DC - solid state

RE9TA51MW

 **Discontinued on:** 1 Jun 2016

EAN Code: 3389110332902

 **Discontinued**

Main

Range Of Product	Zelio Time
Product Or Component Type	Industrial timing relay
Discrete Output Type	Solid state
Component Name	RE9
Time Delay Type	A
Time Delay Range	40 s...1 h

Complementary

Width Pitch Dimension	22.5 mm
[Us] Rated Supply Voltage	24...240 V AC/DC 50/60 Hz
Voltage Range	0.85...1.1 Us
Connections - Terminals	Screw terminals, 2 x 1.5 mm ² flexible with cable end Screw terminals, 2 x 2.5 mm ² flexible without cable end
Tightening Torque	0.6...1.1 N.m
Setting Accuracy Of Time Delay	< +/- 20 %
Repeat Accuracy	< 1 %
Reset Time	100 ms after time delay period
Temperature Drift	< 0.1 %/°C
Maximum [Ie] Rated Operational Current	0.7 A at 20 °C
Minimum Output Current	10 mA at 20 °C
Overload Current	<= 15 A during 10 ms conforming to VDE 0435 (part 303), 4.8.3/class II
Maximum Voltage Drop	<3 V at closed state0.7 A
Maximum Leakage Current	6 mA open contact(s)
Maximum Power Dissipation In W	2.5 W
Electrical Durability	100000000 cycles
Marking	CE
Overvoltage Category	III conforming to IEC 60664-1
[Ui] Rated Insulation Voltage	250 V conforming to IEC 300 V conforming to CSA
Supply Disconnection Value	> 0.1 Uc
Operating Position	Any position without derating

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Surge Withstand	2 kV conforming to IEC 61000-4-5 level 3
Cad Overall Width	22.5 mm
Cad Overall Height	78 mm
Cad Overall Depth	80 mm
Net Weight	0.11 kg

Environment

Immunity To Microbreaks	100 ms during time delay period 2 ms after time delay period
Derating Factor	None >20 °C
Standards	EN/IEC 61812-1
Product Certifications	CSA UL GL
Ambient Air Temperature For Storage	-40...85 °C
Ambient Air Temperature For Operation	-20...60 °C
Relative Humidity	15...85 % 3K3 conforming to IEC 60721-3-3
Vibration Resistance	0.35 mm (f= 10...55 Hz) conforming to IEC 60068-2-6
Shock Resistance	15 gn for 11 ms conforming to IEC 60068-2-27
Ip Degree Of Protection	IP20 (terminals) IP50 (housing)
Pollution Degree	3 conforming to IEC 60664-1
Dielectric Strength	2.5 kV
Non-Dissipating Shock Wave	4.8 kV
Resistance To Electrostatic Discharge	6 kV (in contact) conforming to IEC 61000-4-2 level 3 8 kV (in air) conforming to IEC 61000-4-2 level 3
Resistance To Electromagnetic Fields	10 V/m conforming to IEC 61000-4-3 level 3
Resistance To Fast Transients	2 kV conforming to IEC 61000-4-4 level 3
Disturbance Radiated/Conducted	CISPR 11 group 1 - class A CISPR 22 - class A

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1


Contractual warranty

Warranty	18 months
----------	-----------


Dimensions Drawings

Width 22.5 mm

Rail Mounting




Screw Fixing




Connections and Schema

Internal Wiring Diagram



Recommended Application Wiring Diagram



The timing relay is placed in series, with the load whose energisation is to be delayed on one side and switch K on the other side. The mains supply may be a.c. or d.c. and the voltage may be between 24 V and 240 V.

Technical Description

Function A : Power on Delay Relay


Description

The timing period T begins on energisation. After timing, the output(s) R close(s). The second output can be either timed or instantaneous.

Function: 1 Output





Function: 2 Outputs



2 timed outputs (R1/R2) or 1 timed output (R1) and 1 instantaneous output (R2 inst.)

Legend

	Relay de-energised
	Relay energised
	Output open
	Output closed

C	Control contact
G	Gate
R	Relay or solid state output
R1/R2	2 timed outputs
R2 inst.	The second output is instantaneous if the right position is selected
T	Timing period
Ta -	Adjustable On-delay
Tr -	Adjustable Off-delay
U	Supply