

Product data sheet

Specifications

SQUARE D



Non-Reversing Starter Size 1, 3-Pole, Melting Alloy Overload, Nema 1 +Options

8536SCG3V84CFF4TX22

Price*: 2,120.00 USD

! Discontinued

Main

Product Type	Starter
Product Range	S
Starter Type	Non reversing

Complementary

Nema Size	1
Rated Current	27 A
Number Of Poles	3P
Maximum Voltage Rating	600 V AC
Phase	3 phase
Type Of Overload	Melting alloy 3
Horsepower Rating	7.5 HP 200 V AC 7.5 HP 230 V AC 10 HP 460 V AC 10 HP 575 V AC
Coil Voltage	120 V AC 60 Hz secondary circuit 208 V AC 60 Hz primary circuit
Control Circuit Type	Control circuit transformer
Control Units	Selector switch (HAND-OFF-AUTO)
Auxiliary Contacts	2 NO + 2 NC
Other Equipment	2 fuses (primary), 1 fuse (secondary)
Terminal Type	Screw clamp terminals
Height	15.87 in (403 mm)
Width	6.34 in (161 mm)
Depth	5.20 in (132 mm)

Environment

Enclosure Type	NEMA 1 painted sheet steel
Certifications	NEMA CSA UL Listed

Ordering and shipping details

Discount Schedule	CP1
-------------------	-----

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Returnability	No
Country Of Origin	US

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive

Not applicable, out of EU RoHS legal scope