

Product datasheet

Specifications



LoadCentre KQ - type B split metered distribution board - 250A - 14 + 6 TP ways

SEB42S18250

EAN Code: 5018934961743

Main

| | |
|---------------------------|---|
| Range | Acti9 |
| Product Name | Load centre KQ II B |
| Product Or Component Type | Distribution board |
| Device Application | Distribution |
| Enclosure Type | Split meter |
| Door Type | Overall |
| Provided Equipment | Enclosure Door Front cover Multi-function meter - 2 nos. Shielded neutral bar 25 mm ² Earth terminal block 25 mm ² Pan assembly |
| Colour | Grey (RAL 7035) |

Complementary

| | |
|--------------------------------|--|
| Enclosure Mounting | Surface |
| [Ie] Rated Operational Current | 250 A at 400/415 V AC |
| Incomer Device Options | Switch disconnector - 4P MCCB - 4P |
| Protection Device Options | Miniature circuit breaker (MCB) (plug-on type) as outgoer Residual current circuit breaker with overcurrent protection (RCBO) (plug-on type) as outgoer |
| Number Of Ways | 14 ways (3P)outgoer for section 1 6 ways (3P)outgoer for section 2 |
| Cable Entry | top and bottom: knock-out side: knock-out |
| Height | 1290 mm |
| Width | 470 mm |
| Depth | 139 mm |

Environment

| | |
|-------------------------|--|
| Ip Degree Of Protection | IP2x B internal conforming to BS EN 60529 IP3x external conforming to BS EN 60529 |
|-------------------------|--|

Packing Units

| | |
|------------------------------|-----|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|------------------|----------|
| Package 1 Height | 15.0 cm |
| Package 1 Width | 54.0 cm |
| Package 1 Length | 145.0 cm |
| Package 1 Weight | 28.0 kg |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Sustainability



Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

| | |
|--|---|
|  Mercury Free | |
|  Rohs Exemption Information | Yes |
| Reach Regulation | REACH Declaration |
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
| China Rohs Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information |