# **Product datasheet**

Specifications





# Solid state relay, 2 A, zero voltage switching, input 15...30 V DC, output 24...280 V AC

Local distributor code: 403013568

SSL1A12BD

#### EAN Code: 3606480579721

#### Main

Range Of Product	Harmony Solid State Relays	
Product Or Component Type	Solid state relay up to 10 A	
Device Short Name	SSL	
Network Number Of Phases	1 phase	
Output Switching Mode	DC switching	

### nlomontary

Complementary		
Mounting Support	Socket	
[In] Rated Current	2 A	
Output Voltage	24280 V AC	
[Uc] Control Circuit Voltage	1530 V DC	
Capacitance Unbalance	1.5 pF input/output	
Minimum Switching Voltage	15 V DC turn-on	
Maximum Switching Voltage	10 V DC turn-off	
Input Current Limits	6 mA	
Input Impedance	3500 Ohm	
Solid State Output Type	Zero voltage switching SCR output	
Load Current	0.072 A	
Tansient Overvoltage	600 V AC	
Surge Current	120 A for 16.6 ms 115 A for 20 ms	
Maximum Voltage Drop	<1.1 V on-state	
Maximum I <sup>2</sup> T For Fusing	66 A².s for 10 ms at 50 Hz 60 A².s for 8.3 ms at 60 Hz	
Maximum Leakage Current	4 mA off-state	
Dv/Dt	500 V/µs off-state at maximum voltage	
Response Time	0.5 cycle (turn-on) 0.5 cycle (turn-off)	
Overvoltage Category	III	
Width	5 mm	
Height	28 mm	
Depth	15 mm	

Net Weight

Environment		
Flame Retardance	V0 conforming to UL 94	
Dielectric Strength	2500 V for input/output	
Pollution Degree	2	
Product Certifications	UL CSA	
Marking	CE	
Ambient Air Temperature For Operation	-2080 °C	
Ambient Air Temperature For Storage	-2085 °C	

# **Packing Units**

•	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.7 cm
Package 1 Width	2.5 cm
Package 1 Length	37 cm
Package 1 Weight	5 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	12
Package 2 Height	0.7 cm
Package 2 Width	2.5 cm
Package 2 Length	37 cm
Package 2 Weight	61 g
Unit Type Of Package 3	S01
Number Of Units In Package 3	1080
Package 3 Height	15 cm
Package 3 Width	15 cm
Package 3 Length	40 cm
Package 3 Weight	5.684 kg

### **Contractual warranty**

Warranty

18 months

## Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

### Well-being performance

Reach Free Of Svhc
Mercury Free
Rohs Exemption Information Yes


### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information

### **Product datasheet**


### **Dimensions Drawings**

#### Dimensions



**Performance Curves** 

#### **Derating Curves**



A : Load Current (Amperes) B : Ambient Temperature (°C)