Product datasheet

Specification





TeSys Vario enclosed, emergency switch disconnector, 63A, IP65

Local distributor code:

22427881 VCF4GE

EAN Code: 3389110543902

Main

| Range | TeSys |
|---------------------------|---|
| Product Name | TeSys VARIO |
| Device Short Name | VCF |
| Product Or Component Type | Enclosed emergency stop switch disconnector |
| Performance Level | High performance |
| Poles Description | 3P |
| Control Type | Rotary handle |
| Handle Colour | Red |
| Handle Front Plate Colour | Yellow |
| Rotary Handle Padlocking | 1 to 3 padlocks 48 mm |

Complementary

| Complementary | |
|---|--|
| Marking | 0 - 1 |
| [Ue] Rated Operational Voltage | 690 V AC |
| [Uimp] Rated Impulse Withstand Voltage | 8 kV |
| [Ithe] Conventional Enclosed Thermal Current | 63 A |
| [le] Rated Operational Current | 57 A (AC-23A) at 400 V |
| Rated Operational Power In W | 30 kW at 400 V (AC-23) 22 kW at 400 V (AC-3) |
| Intermittent Duty Class | 30 |
| Making Capacity (I Rms) | 800 A at 400 V AC-21A 800 A at 400 V AC-22A 800 A at 400 V AC-23A |
| [Icm] Rated Short-Circuit Making Capacity | 2.1 kA at 400 V at Ipeak |
| [Icw] Rated Short-Time Withstand Rms Current | 960 A at 400 V duration: 1 s |
| Rated Conditional Short-Circuit Current | 10 kA at 400 V - associated fuse 80 A aM 10 kA at 400 V - associated fuse 80 A gG |
| Breaking Capacity | 640 A at 400 V (AC-21A) 640 A at 400 V (AC-22A) 640 A at 400 V (AC-23A) |
| Mechanical Durability | 30000 cycles |
| Electrical Durability | 30000 cycles AC-21 30000 cycles DC-15 |
| Environmental Characteristic | Standard environment |

| Suitability For Isolation | Yes | |
|------------------------------|--|--|
| Connections - Terminals | Screw clamp terminals16 mm² - flexible - with cable end Screw clamp terminals25 mm² - solid | |
| Tightening Torque | 4 N.m - on screw clamp terminals | |
| Fire Resistance | 960 °C conforming to IEC 60595-2-1 | |
| Handle Front Plate Dimension | 60 x 60 mm | |
| Height | 180 mm | |
| Width | 157 mm | |
| Depth | 152 mm | |
| Net Weight | 0.93 kg | |

Environment

| Standards | IEC 60947-4-1 IEC 60204 |
|---------------------------------------|---|
| Protective Treatment | TC |
| Ip Degree Of Protection | IP65 conforming to IEC 60529 |
| Mechanical Robustness | Vibrations 10150 Hz (1 gn) conforming to IEC 60068-2-6 Shocks 11 ms (30 Gn) conforming to IEC 60068-2-27 |
| Ambient Air Temperature For Operation | -2050 °C |

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|-----------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 16.800 cm |
| Package 1 Width | 18.600 cm |
| Package 1 Length | 19.600 cm |
| Package 1 Weight | 923.000 g |
| Unit Type Of Package 2 | P06 |
| Number Of Units In Package 2 | 32 |
| Package 2 Height | 80.000 cm |
| Package 2 Width | 80.000 cm |
| Package 2 Length | 60.000 cm |
| Package 2 Weight | 43.210 kg |

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

✓ Toxic Heavy Metal Free
 ✓ Mercury Free
 ✓ Rohs Exemption Information

Certifications & Standards

| Reach Regulation | REACh Declaration |
|--------------------------|---|
| Eu Rohs Directive | Compliant with Exemptions |
| China Rohs Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information |
| Environmental Disclosure | Product Environmental Profile |
| Weee | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |
| Circularity Profile | No need of specific recycling operations |