

# Product data sheet

Specifications

SQUARE D



## 2SPEED STARTER 600VAC 90A NEMA

8810SEO1V03

 To be discontinued on: Sep 30, 2024

Product availability: Non-Stock - Not normally stocked in distribution facility

 To be discontinued

### Main

Device Short Name	S
-------------------	---

### Complementary

Depth	7 in (177.80 mm)
Device Mounting	Surface
Height	14.44 in (366.78 mm)
Maximum Horse Power Rating	20 hp 200 V AC, 3 phase 25 hp 230 V AC, 3 phase 40 hp 460/575 V AC, 3 phase
Motor Type	Single winding constant horsepower
Nema Size	3
Number Of Poles	3
Number Of Thermal Units Required	6
Width	18 in (457.20 mm)

### Environment

Product Certifications	UL Listed NEMA
------------------------	-------------------

### Ordering and shipping details

Category	21302 - 8810,11,12 S
Discount Schedule	CP1
Gtin	785901191070
Returnability	No
Country Of Origin	MX

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	14.45 in (36.7 cm)
Package 1 Width	17.99 in (45.7 cm)
Package 1 Length	7.01 in (17.8 cm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Weight	45.50 lb(US) (20.639 kg)
------------------	--------------------------

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive

Not compliant

---