# Product data sheet

Specifications





# Contactor, Type L, multipole lighting, electrically held, 30A, 8 pole, 600 V, 110/120 VAC 50/60 Hz coil, NEMA 1 flush

8903LF80V02

Product availability: Non-Stock - Not normally stocked in distribution facility

#### Main

| Product Or Component Type | Electrically Held Lighting Contactor |  |
|---------------------------|--------------------------------------|--|
| Range Of Product          | 8903L                                |  |
| Control Circuit           | Separate control circuit             |  |

### Complementary

| oompiementary                   |                                   |  |
|---------------------------------|-----------------------------------|--|
| Control Circuit Voltage         | 110 V AC 50 Hz<br>120 V AC 60 Hz  |  |
| Inrush Power In Va              | 180 VA 60 Hz<br>170 VA 50 Hz      |  |
| Hold-In Power Consumption In Va | 35 VA 60 Hz<br>35 VA 50 Hz        |  |
| Current Rating                  | 20 A tungsten<br>30 A fluorescent |  |
| Number Of Poles                 | 8P 8 NO                           |  |
| Control Unit                    | No control units                  |  |
| Pilot Light                     | No indicator                      |  |
| Electrical Connection           | Screw-clamp terminals             |  |
| Height                          | 15.20 in (386 mm)                 |  |
| Depth                           | 5.43 in (138 mm)                  |  |
| Width                           | 8.94 in (227 mm)                  |  |

#### Environment

| Enclosure Type         | NEMA 1 painted sheet steel flush |
|------------------------|----------------------------------|
| Product Certifications | UL Listed<br>CSA                 |

### Ordering and shipping details

| Category          | 21321 - 8903 L (NOT LX) |  |
|-------------------|-------------------------|--|
| Discount Schedule | CP1                     |  |
| Gtin              | 785901022121            |  |
| Returnability     | No                      |  |
| Country Of Origin | MX                      |  |

## **Packing Units**

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

| Unit Type Of Package 1       | PCE                     |
|------------------------------|-------------------------|
| Number Of Units In Package 1 | 1                       |
| Package 1 Height             | 15.20 in (38.6 cm)      |
| Package 1 Width              | 8.94 in (22.7 cm)       |
| Package 1 Length             | 5.43 in (13.8 cm)       |
| Package 1 Weight             | 39.42 lb(US) (17.88 kg) |

### **Contractual warranty**

Warranty

18 months

## Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

### Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes
Pvc Free
Halogen Free Plastic Parts Product

### **Certifications & Standards**

| Reach Regulation         | REACh Declaration                                                                           |
|--------------------------|---------------------------------------------------------------------------------------------|
| Eu Rohs Directive        | Compliant<br>EU RoHS Declaration                                                            |
| China Rohs Regulation    | China RoHS declaration<br>Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | Product Environmental Profile                                                               |
| Circularity Profile      | No need of specific recycling operations                                                    |